

## **DEEP REGRESSED ARCHITECTURAL ALUMINUM MOUNTING CHANNEL**

PROJECT	ТҮРЕ
CATALOG NUMBER	

# **LED-CHL-D**

### **PRODUCT DESCRIPTION**

Extruded deep regressed aluminum channel with slide in frosted glossy lens that provides a rigid, deep set linear mounting platform for the following GM Lighting LEDTask Flexible LED Linear Ribbons:

For the following L	.EDTask™ Flexible Linear Ribbon Series
LTR60/300 Series	12VDC High Output - Dry and Wet location
LTR60/300-SO Series	12VDC Standard Output - Dry and Wet location
GM100-24 Series	24VDC Standard Output - Dry and Wet location
LTR30024 Series	24VDC High Output - Dry and Wet location
LTR150-RGB Series	12VDC RGB Series - Dry location

## **MOUNTING**


Mount into 34"W recessed channel using included mounting clips and screws or adhesive (by others).

Flexible LED linear ribbon uses attached 3M mounting tape. Use LED-CHL-D-EC endcaps for a finished look. Ordered separately.

### LENS:


Comes with frosted glossy lens.

PLEASE ALLOW THE FOLLOWING
VISUAL CLEARANCE TO ALLOW FOR
FLEXIBLE RIBBON TO RIBBON CONNECTORS



NOTE: Channels may not accommodate all ribbon to ribbon and ribbon to power supply connections. Please locate connections outside of channel interior.

Accessories	
LED-CHL-D-EC	Solid end caps (2) for LED-CHL-D End
LED-CHL-D-EC-H	caps with holes (2) for LED-CHL-D



Model Number	Description	Length	Height	Width	Finish
LED-CHL-D	Deep regressed architectural aluminum channel	48"	1/2"	5/8"	Brushed Aluminum