

12VDC SILICONE DAMP LOCATION FLEXIBLE LED LINEAR RIBBON INSTALLATION KIT

Connecting GM Lighting's 12V SLR Damp Location LED Linear Ribbon need not be done by the experts. GM Lighting's SLRK-48 installation kit includes everything you need to make a quick and professional looking installation. The SLR Ribbons, the connectors, an end cap - even the power supply.

Kit includes:

- 1 - 8 inch 12VDC LED Ribbon
- 1 - 16 inch 12VDC LED Ribbon
- 1 - 24 inch 12VDC LED Ribbon
- 1 - LED Ribbon to Power Supply Connector
- 1 - 3 inch Ribbon to Ribbon Connector
- 1 - 12 inch Ribbon to Ribbon Connector
- 1 - 'L' Connector
- 1 - Female End Cap for LED Ribbon
- 1 - Female End Cap for LED Ribbon
- 1 - Male End Cap for LED Ribbon
- 1 - 12VDC ETL listed Power Supply
- 1 - Cut End Cap



SLRK-48
12 inch ribbon to ribbon connector with end cap.



Ribbon to power supply connector.



3 inch ribbon to ribbon connector with end cap.

SLR Ribbon Section



The kit comes with 3 lengths of damp location LED flexible ribbon: 8", 16" and 24". For longer lengths, please see the SLR ribbon on pages 23-24.

Catalog No.	Description	Ribbon Lengths	Connectors	Power Supply
SLRK-48	12VDC damp location SLR LED Linear Ribbon installation kit complete with ribbon, connectors and power supply	24" 16" 8"	3", 12", L-Type Ribbon to Power Supply Female and Male End Caps Cut End Cap	12VDC ETL listed