

# 120V/12V LumenTask™ Xenon Undercabinet

One piece, low profile (1-3/8" height) 18 gauge CRS housing with diecast ends for stability.

Designer gloss white powder coat paint finish. Also available in powder coat bronze and solid stainless steel.

Mounting hole with pre-set screws for easy alignment and installation.

Multiple vents for cool undercabinet operation.

Ceramic lamp socket

Open Wide wiring compartment

Anodized aluminum mirrored reflector.

Tempered, prismatic frosted glass lens that slides in for easy installation.

Hi-Low-Off switch enables full or 50% lighting level.

Die cast end caps

4" O.C.

Model	Length	Width	Height	Knock-outs
X8	8"	4-3/8"	1-3/8"	6 x 1/2"
X16	16"			10 x 1/2"
X24	24"			14 x 1/2"
X32	32"			18 x 1/2"



## Xenon Lamp

- Ceramic base
- Easy to install
- Eliminate breakage

Multiple knock-outs on top, back and end caps. Wire mold knock-outs on end caps only. Look for optional connectors for multiple unit connection. See page 5.

## Product Information



### 120 Volt: 8" 1 lamp - 1 x 35W

Catalog No.	Voltage	Finish
X8-120-WH	120V	White
X8-120-BZ	120V	Bronze
X8-120-SS	120V	Stainless Steel

### 12 Volt: 8" 1 lamp - 1 x 18W

Catalog No.	Voltage	Finish
X8-12-WH	12V	White
X8-12-BZ	12V	Bronze
X8-12-SS	12V	Stainless Steel

### 120 Volt: 16" 2 lamp - 2 x 35W

Catalog No.	Voltage	Finish
X16-120-WH	120V	White
X16-120-BZ	120V	Bronze
X16-120-SS	120V	Stainless Steel

### 12 Volt: 16" 2 lamp - 2 x 18W

Catalog No.	Voltage	Finish
X16-12-WH	12V	White
X16-12-BZ	12V	Bronze
X16-12-SS	12V	Stainless Steel

### 120 Volt: 24" 3 lamp - 3 x 35W

Catalog No.	Voltage	Finish
X24-120-WH	120V	White
X24-120-BZ	120V	Bronze
X24-120-SS	120V	Stainless Steel

### 12 Volt: 24" 3 lamp - 3 x 18W

Catalog No.	Voltage	Finish
X24-12-WH	12V	White
X24-12-BZ	12V	Bronze
X24-12-SS	12V	Stainless Steel

### 120 Volt: 32" 4 lamp - 4 x 35W

Catalog No.	Voltage	Finish
X32-120-WH	120V	White
X32-120-BZ	120V	Bronze
X32-120-SS	120V	Stainless Steel

### 12 Volt: 32" 4 lamp - 4 x 18W

Catalog No.	Voltage	Finish
X32-12-WH	12V	White
X32-12-BZ	12V	Bronze
X32-12-SS	12V	Stainless Steel

Replacement lamp: 120V - G9-120VCL - 35W Xenon (page 21)

Replacement lamp: 12V - G6.35-12VCL - 18W Xenon (page 21)