

LUMENTASK™ 120V LED UNDERCABINET



UCLED-24-WH

With the rising costs of energy, both home and business owners are looking for ways to not only cut down on their energy expenses, but also to utilize more earth friendly light sources. GM Lighting's LumenTask™ LED undercabinet fixtures achieves both of these concerns while offering an attractive and low maintenance product, and now available as a dimmable fixture.

- 120V direct wiring • Integral LED power supply
- No remote power supply required
- Low wattage consumption • 50,000 hour LED life
- No harmful UV rays • 3000K warm white
- (DIM) models use standard Triac dimmer (on-off switch only). Dimming to 10%.

Model	Length	Knock-outs
UCLED-8	8"	3 X 1/2"
UCLED-16	16"	5 X 1/2"
UCLED-24	24"	7 X 1/2"



Multiple knock-outs on back. End caps feature a standard / Wiremold™ combination knock-out. Look for optional connectors for multiple unit connection on page 48.

Catalog No.	Diode	No. of Diodes	Total Wattage per Fixture*	Lumens**		Length	Finish
				Hi	Low		
UCLED-8-WH	LED	3	11W	189	101	8"	White
UCLED-8-BZ	LED	3	11W	189	101	8"	Bronze
UCLED-8-SS	LED	3	11W	189	101	8"	Stainless Steel
UCLED-16-WH	LED	5	17W	300	163	16"	White
UCLED-16-BZ	LED	5	17W	300	163	16"	Bronze
UCLED-16-SS	LED	5	17W	300	163	16"	Stainless Steel
UCLED-24-WH	LED	8	24W	428	232	24"	White
UCLED-24-BZ	LED	8	24W	428	232	24"	Bronze
UCLED-24-SS	LED	8	24W	428	232	24"	Stainless Steel
UCLED-8-WH-DIM	LED	3	11W	189	N/A	8"	White
UCLED-8-BZ-DIM	LED	3	11W	189	N/A	8"	Bronze
UCLED-8-SS-DIM	LED	3	11W	189	N/A	8"	Stainless Steel
UCLED-16-WH-DIM	LED	5	17W	300	N/A	16"	White
UCLED-16-BZ-DIM	LED	5	17W	300	N/A	16"	Bronze
UCLED-16-SS-DIM	LED	5	17W	300	N/A	16"	Stainless Steel
UCLED-24-WH-DIM	LED	8	24W	428	N/A	24"	White
UCLED-24-BZ-DIM	LED	8	24W	428	N/A	24"	Bronze
UCLED-24-SS-DIM	LED	8	24W	428	N/A	24"	Stainless Steel

*Total wattage includes power supply.

** Lumens for hi and low switch positions.

Key to LED LumenTask Diagram: **1.** Hi-Low-Off switch enables full or 50% lighting level (on/off switch in dimmable (DIM) models). **2.** Integral LED power supply. **3.** Tempered frosted, prismatic glass lens that slides in for easy installation. **4.** LED PCB board. Available in 8", 16" and 24".

See page 48 for accessories and replacement lenses.

