

LEDTASK™ 24VDC STANDARD OUTPUT LED LINEAR RIBBON IN A 30M REEL

GM now brings to the lighting market a 24VDC 30M (98.5') reel of field cuttable LED flexible linear ribbon. Perfectly suited for cove lighting, architectural detail illumination, themed lighting, accent lighting, or any linear lighting application that requires long, uninterrupted runs. **NOTE: Each 32' section needs to be wired to the power supply.**



- 24VDC ▪ Dimmable
- No harmful UV rays
- 50,000 hr. LED life
- Cuttable every 6 LED's
- Even illumination
- Utilizes 3M double stick tape
- Accessories allow for multiple configurations



Catalog No.	Color	LED Watts per ft.	Amps per ft.	Lumens per ft.	Length	LED Life
GM100-24-SO-27	2700K Warm White	1.44W per ft.	0.6	80	30M (98.5 ft.)	50,000 hrs.
GM100-24-SO-WW	3500K Warm White	1.44W per ft.	0.6	95	30M (98.5 ft.)	50,000 hrs.
GM100-24-SO-PW	5500K Pure White	1.44W per ft.	0.6	125	30M (98.5 ft.)	50,000 hrs.

Please see Quick Reference Guide on page 41 for maximum single runs. See page 61 for power supplies. Kelvin temperature (color) ±200K.