



PRODUCT DESCRIPTION

TWIST-TASK™ is a high output, 90+ CRI flexible LED linear tape that is segmented, enabling intricate mounting that follows complex shapes and forms. 3M adhesive mounting back. Available in a 17' (5.18M) reel.

Custom lengths available - consult factory

Power supplies are available - see page 91

12
VOLT

DRY
LOCATION

90+
CRI

CLASS
2

FIELD
CUTTABLE

5 Yr.
WARRANTY

NEW! TWIST-TASK™ 12VDC HIGH OUTPUT 90+ CRI FLEXIBLE LED TAPE

KEY FEATURES

- Flexible segmented LED tape that is cuttable in the field (cuttable every 4" / 102mm).
- Mounts with 3M VHB™ double stick tape.
- SureTite™ tape to tape and tape to power supply connectors available (see below).
- Dimmable (see page 101).
- Maximum run on a given lead is 17'.
- Shipped in anti-static packaging.
- Available in 17' (5.18M) reels.

ELECTRICAL

- 12VDC remote power supply required (see page 91).
- Rated at 2.2W per foot.
- 120° viewing angle.
- 50,000 hr. operation.

OPTICS

- 2700K, 3000K, 3500K, 4200K.
- Up to 207 lumens per foot.

CERTIFICATION

- ETL
- IP20 dry location

WARRANTY

- 5 year warranty.



PRODUCT ORDERING MATRIX

Catalog No.	Length	Wattage	Lumens	CRI	Color Temp.*
TWR300-27	17' (5.18M)	2.2W/ft.	189/ft.	90+	2700K
TWR300-30	17' (5.18M)	2.2W/ft.	196/ft.	90+	3000K
TWR300-35	17' (5.18M)	2.2W/ft.	198/ft.	90+	3500K
TWR300-42	17' (5.18M)	2.2W/ft.	207/ft.	90+	4200K

Each 17' reel includes: (3) ESTW-60 Sure-Tite™ connectors and 24" of lead affixed at start of tape

* Kelvin temperature (color) ±200K

CONNECTORS AND ACCESSORIES

Cat. No.	Description
ESTC-1	SureTite™ tape to tape rigid connector
ESTLK-60	60" SureTite™ flexible tape to tape connector
ESTW-60	60" SureTite™ flexible tape to power supply connector

KEY FEATURES

- SureTite™ connectors enable a 'contractor preferred' quality connection.
- ESTLK-60 and ESTW-60 are adjustable to any length desired, and cuttable in the field.



PRODUCT DIAGRAM

