## LED 24VDC MAGNETIC DIMMABLE 60W POWER SUPPLY by

## **GMLighting**

Project:		
•		
Type: ———		
I a a a ti a m.		
Location:		
Contact Phone:		

## **PRODUCT DESCRIPTION**

Smallest dimmable Class II hardwire LED dimming magnetic power supply on the market that works with conventional low voltage magnetic wall mount dimmer with on/off switch. Auto reset thermal circuit breaker on the secondary side.

## **PRODUCT SPECIFICATIONS**

**Construction:** Transformer is encapsulated in all metal construction enclosure. Enclosure temperature should not exceed 70°C (158°F) @ 40°C (104°F) ambient. Wiring compartment has 2 knockouts. Removable cover for wiring compartment is secured in place by screw. Black powder coated.


**Electrical:** Thermal class B-130C. Input leads are 20 AWG. Output leads are 16 AWG. Lead insulation rated to 105°C (221°F). Transformer utilizes a class B 130°C (266°F) insulation system. Maximum load is 60W. Coil former is double section bobbin. Auto reset.


**Dimming:** Works with low-voltage magnetic wall dimmer with on/off switch.

Mounting: Surface mount with front mounting tab.

Warranty: 4 years.

Label: ETL listed for indoor and outdoor use.







Catalog Number	Max. Wattage	Input Voltage	Output Voltage	Input Current	Open Circuit	Output Current	Weight	L D	imensions W	н
LTHM60-DIM-2	24 60W	120V/60Hz	24VDC	500ma	24.5V	2.5A	3.3 lb.	6.06"	2.59"	2.33"

For voltage drop - see www.gmlighting.net/voltagedrop.html or consult GM Lighting Product catalog, page 19.

