

SUPERSEAL® LIQUID TIGHT CONDUIT CSA FT4

SSFT4

Superseal® Type "CSA" - Hydro Tested FT4

- Hot-dipped galvanized steel core with a pressure extruded PVC jacket
- Smooth interior for easy wire pulling
- Bi-directional
- Strength and flexibility to handle stress and strain
- Used in dry, damp or wet locations.
- Resists sunlight, heat and chemical degradation
- PVC jacket 75° C
- CSA # LL63214

Work Temperature: -30° to +75°C



A company as flexible as its product..

SUPERIOR FLEXIBLE CONDUITS INC.

Superseal® CSA FT4

Part #	Trade Sizes (Inches)	Inside Diameter (Inches)	Outside Diameter (Inches)		Weight Per Coil CSA	Bend Diameter (Inches)	Standard Coils (Meters)	Standard Reels (Meters)
			Min.	Max.				
SFT4-038	12 (3/8")	12.29 (.484)	17.5 (0.690)	18.0 (.710)	10 kg	101.6 (4)	30	150/300/360
SFT4-050	16 (1/2")	15.8 (.622)	20.8 (.820)	21.3 (.840)	12 kg	152.4 (6)	30	150/300
SFT4-075	21 (3/4")	20.83 (.820)	25.2 (1.030)	26.7 (1.050)	16 kg	203.2 (8)	30	150
SFT4-100	27 (1")	26.44 (1.041)	32.8 (1.290)	33.4 (1.315)	22 kg	254 (10)	30	120
SFT4-125	35 (1 1/4")	35.05 (1.380)	41.4 (1.630)	42.2 (1.660)	16 kg	318 (12.5)	15	75
SFT4-150	41 (1 1/2")	40.01 (1.575)	47.4 (1.865)	48.3 (1.900)	20 kg	381 (15)	15	45
SFT4-200	53 (2")	51.31 (2.020)	59.4 (2.340)	60.3 (2.375)	25 kg	508 (20)	15	30
SFT4-250	63 (2 1/2")	62.99 (2.480)	72.1 (2.840)	73.0 (2.875)	18 kg	635 (25)	10	
SFT4-300	78 (3")	77.98 (3.070)	87.9 (3.460)	88.9 (3.500)	22 kg	762 (30)	10	
SFT4-400	103 (4")	101.6 (4.000)	113.3 (4.460)	114.3 (4.500)	38 kg	1016 (40)	10	

Custom lengths available upon request. Longer reel lengths are available reel deposit depending on length. Colour-Black. Other colours available upon request (blue, orange, red, yellow) Please contact our office for more details.