



PRO

The PRO range is a portable light that works with high quality lithium-ion batteries and LED chips giving clear bright light for up to 4 hours on one charge, meaning you can push on and get the job done.

The PRO comes with mains and in-car charger so you can charge the battery on the go.

30M BEAM RANGE // FL10CACW

- » SUPER VERSATILE AND LIGHT WEIGHT
- » RANGE OF AVAILABLE ACCESSORIES
- » RECHARGEABLE AND CORDLESS
- » MAINS AND CAR CHARGER INCLUDED

Light source	10W
Dimensions	145 x 240 x 165mm // 5.5 x 9.5 x 6.3 inches
Luminous flux	700+ Lm
Color Temperature	5,500 - 6000K
Color rendering index	RA>70
Housing material	Aluminium and iron
Adaptor (input)	100-240V AC 50/60Hz
Operating temperature	-25°C to 50°C // -13°F to 122°F
Charge temperature	0°C to 40°C // 32°F to 113°F
Beam angle	120°
Battery specifications	7.4V 4.4Ah Li-ion
Charging time	5 Hours
Working time	4 Hours*
Certificates	CE / RoHS / UL / CSA / IP65
Warranty	2 Years



*Battery life may vary based on your use



FREE CAR CHARGER INCLUDED!