

## Arlington

## Low Profile IN BOX™ for **New Construction** Stucco, Textured Surfaces, and Rigid Siding

One-piece, recessed electrical box with weatherproof-in-use cover for stucco over masonry or wood construction. Also for cementitious/fiber rigid lap siding. Non-metallic cover and base. Accepts most single gang wiring devices and uses standard indoor wall plates or a GFCI cover plate. Box and white cover are textured/ paintable. UV rated plastic for long outdoor life.



Features and Benefits

- · One-piece assembly replaces the installation of an electrical box and bubble cover assembly
- · Installs in the wall, so less of it shows outside
- · Holes in flange allow stucco to bond firmly
- · Install option: Cover is removable for easier device installation

Scan For Video

| CATALOG<br>NUMBER | UPC/DCI/NAED<br>MFG #018997 | ORIENTATION/<br>COVER COLOR | UNIT<br>PKG | М. | DIM<br>A | DIM<br>B | DIM<br>C | DIM<br>D | DIM<br>E |
|-------------------|-----------------------------|-----------------------------|-------------|----|----------|----------|----------|----------|----------|
| DBVM1C            | 14315                       | Vertical/Clear              | 1           | 4  | 9.058    | 7.012    | 5.160    | 1.805    | 3.222    |
| DBVM1W            | 14316                       | Vertical/White              | 1           | 4  | 9.058    | 7.012    | 5.160    | 1.805    | 3.222    |
| DBHM1C            | 77608                       | Horizontal/Clear            | 1           | 4  | 7.012    | 9.058    | 5.160    | 1.805    | 3.222    |
| DBHM1W            | 77610                       | Horizontal/White            | 1           | 4  | 7.012    | 9.058    | 5.160    | 1.805    | 3.222    |

Add suffix "GC" to Catalog # when ordering in Canada, for example DBVM1CGC.


Replacement covers available on page K-17. 2-Gang style available on page K-8.




WEATHERPROOF-IN-USE



**Bug Plugs** ship installed in all IN BOX styles to seal unused cord hole openings.





IN BOX for new stucco, textured surfaces, and rigid siding includes...Box with weatherproof-in-use cover; installed bug plugs; (1) standard duplex and (1) standard GFCI face plate; (1) NM cable connector; block bushing with washer; and an in-place, disposable mud cover.

Note: Additional Installation Methods shown on page J-13.

## Installation Instructions for New Masonry Construction





Make a 3-1/4" x 5-1/2" hole in block. Pull wiring through plastic and wire. Attach recessed block bushing and opening in block. Block bushing mounts to interior side of block.




Install NM cable connector IN BOX to block. Holes in flange allow stucco to bond firmly.



Install wiring device per manufacturer's instructions, Local, and National Electrical Codes. Accepts most devices and a standard indoor wall plate.



Completed installation with weatherproof-in-use cover. DBVM1C shown.



Note: Meets 2011 NEC Section 406-9; for the protection of exterior outlets which require the use of a weatherproof while-in-use cover for all outdoor 15 or 20 AMP receptacles.