Outlet Box with Threaded Openings

More on

The Easy Way to add an Outlet Box later



UPC/DEI/NAED Unit Catalog Description Std Number Mfg. #018997 Outlet Box w/ Two Threaded Openings Pkg Pkg FS8161T 10 10 00873 for Flat Surfaces for 1/4" or 5/16" Rigid Siding FS8131T 00870 10 10 FS8141T 00871 for 1/2" Siding 10 10 FS8151T 10 10 00872 for 5/8" Siding FS8171T 00874 for Dutch Lap Siding 10 10

Includes (2) 1/2" NPT plugs

outlet boxes.

FS8161T

for flat surfaces

Install a receptacle where you need it; add another outlet box later. It's easy

with Arlington's non-metallic

Saves Time. Convenient!

The FS8161T box gives you the option of installing the receptacle where you need it — in horizontal or vertical orientation. The threaded openings allow for the installation of additional outlet boxes at a later time.

Convenient and versatile, FS8161T is designed for flat surfaces. We also have an adapter plate for each siding type that converts the FS8161T outlet box for use on all siding types.

- Non-metallic, UV-rated
- Includes two threaded openings
- Installs devices on flat, exterior surfaces. Use with adapter plate for installations on any siding type
- Textured, paintable finish



1 Stauffer Industrial Park Scranton, PA 18517 800/233.4717 Fax 570/562.0646 www.aifittings.com

Outlet Box with Threaded Openings

For Flat Surfaces and Any Siding Type

FS8161T Installation on Flat Surfaces



1 Pull wire. Attach box to flat surface.





3 Use threaded opening(s) and PVC conduit to install additional outlet boxes.

FS8171T Installation on Dutch Lap Siding



1 Pull wire. Attach the appropriate adapter to the FS8161T box and install on siding.



2 Install receptacle.



3 Use the threaded openings to add another **Outlet Box!**

Use the threaded openings to add another Outlet Box!



1 Stauffer Industrial Park Scranton, PA 18517 800/233.4717 Fax 570/562.0646 www.aifittings.com

ES8161T etc 0608/50M



Adapter plates convert the FS8161T box for flat surfaces into an outlet box that can be used on any siding type.

- · Includes two threaded openings
- Non-metallic
- Installs devices on any siding type
- · Textured, paintable finish

UV-rated



Distributed by