



Non-metallic FR Series Device & **Fixture Box**

Flanged, reversible box for two different depths. Back panel works on either end of the box for both 1/2" or 1-1/4" depths. For new construction. Use for mounting coach lights on stucco and/or flat siding.










Features and Benefits


- Wall mount one-piece design for new installations
- Up to a 10 lb. fixture rating
- Ships with 1-1/4" box depth for foam/stucco applications
- · Easily converts to 1/2" box depth by removing and reinstalling back plate
- The fixed flange is large enough to eliminate the need for a separate flashing
- No gasket needed to seal box from air infiltration
- Large 20 cubic inch volume
- · Made of high strength polycarbonate

CATALOG NUMBER	UPC/DCI/NAED MFG #018997	APPLICATION	UNIT PKG		DIM A	DIM B	DIM C	DIM D
FR101F	12680	Device Box	10	10	7.875	7.125	3.750	3.525
FR405F	12681	Pan Box	10	10	6.750	6.750	4.000	1.375
FR420F	09615	Fixture Box	10	10	6.750	6.750	4.000	1.986



1





Installation Instructions



Re-install the back on the OPPOSITE side of the box.



For 5/8" wall finish thickness, loosen two screws and

remove the back.

Install supplied NM94 cable connector and NM900 plug as needed. Pull wire. Install box.

L-8



For 7/8" wall finish thickness install the 1/4" extension ring



Assembled for 5/8" finish thickness.



...to the front of the box.