

Low-Profile Strain Relief Cord Connectors

Non-metallic. Liquid-tight • Oil-tight. Furnished with sealing ring and locknut.



WHITE SEALING RING MATCHES PRODUCT



CATALOG NUMBER	UPC/DCI/NAED MFG #018997	TRADE SIZE	CORD RANGE	UNIT PKG	STD PKG	DIM A	DIM B	DIM C
LPCG503*	50350	1/2	.100-.300	25	100	1.792	.630	1.042
LPCG50W	32875	1/2	.200-.472	25	100	1.792	.630	1.042
LPCG50*	80086	1/2	.200-.472	25	100	1.792	.630	1.042
LPCG507	50354	1/2	.385-.750	25	100	2.178	.517	1.305
LPCG753*	50760	3/4	.100-.300	10	50	1.963	.570	1.042
LPCG754	50762	3/4	.240-.472	10	50	1.963	.570	1.305
LPCG757	36100	3/4	.385-.750	10	50	2.250	.600	1.305
50LPCGBAG▲	55080	1/2	.100-.472	-	500	1.792	.630	1.042
75LPCGBAG▲	55082	3/4	.100-.472	-	100	1.963	.570	1.305




* UL not applicable for under .240 wire diameter -- wire strength will not meet UL's 35lb test requirement for the fitting.

▲ Includes UF grommet 14/2 to 12/2 and cord grommet .100 to .300. Bags not available in black.

When ordering in black, add suffix "BL" to catalog number.
When ordering in white, add suffix "W" to catalog number.

PATENTED.



Arlington's Low Profile Cord Connector has a unique grommet with gripping fingers. These connectors have the largest cord range in the industry, so there are fewer items to stock. A liquid-tight seal and superior pullout resistance is accomplished by just tightening the nut. A sealing ring is furnished to assure a liquid-tight seal when installing in non-threaded openings.