

QuickPort® High Density Field Configurable Patch Panels

QuickPort® High Density Field Configurable Patch Panels

APPLICATION

Field configurable. Rack-mount high-density patch panel compatible with all QuickPort® modules to maximize versatility and enable easy upgrades and mixture of media types.

STANDARDS COMPLIANCE

Meets or exceeds all applicable standards: UL Listed; CSA Certified; complies with TIA/EIA-568-B; and meets FCC Part 68.

PHYSICAL SPECIFICATIONS

Capacity: 24- and 48-port
Materials: .600" steel; matte black painted finish with white silkscreening.
Dimensions: 24-port: 1.75"H x 19"W x 3.5"D
48-port: 3.5"H x 19"W x 3.5"D
Mounting: 19" rack mount
Color: Black


DESIGN CONSIDERATIONS

- Mounts on 19" wide equipment racks or hinged wall mount brackets (PN# 49251-W6x).
- Accepts all QuickPort modules
- Includes rear wire management bar
- Flush mount
- Write-on blocks and port numbers are silkscreened in white

UNIQUE FEATURES

- High density equal to 110 Term (non-field configurable) Patch Panels.
- Rear wire management support bar.
- Front write-on label areas.

See ELECTRONIC FILES for CAD files (.DXF, .DWG, MS-DOS.EPS) on disk



For ELECTRONIC Typical Specs see (.TXT) file on disk.

TYPICAL SPECIFICATION

Patch panel shall be field configurable 24 port density in 1.75"H rack space and 48 port density in 3.5" (2) rackspaces. Rear wire management bracket shall be included. Typical front labeling of traditional patch panels. Panel shall accept full range of manufacturer's connectors. The manufacturer shall provide a one-year limited product warranty and 15 year product performance guarantee. The manufacturer shall provide a lifetime warranty against defects in material and workmanship, and an application guarantee when installed as part of a certified system.

WARRANTY INFORMATION

- One-year limited product warranty and 15-year performance guarantee are standard.
- Product and performance warranties are extended to a Lifetime as part of Leviton's Certified Cabling System.




For Applications Engineering Support – Call 1-425-485-4288; in USA call 1-800-722-2082
Spec sheets and updates are also available at www.levitonvoicedata.com.

QuickPort® High Density Field Configurable Patch Panels

Part Numbers
49255-H24 49255-H48

DIMENSIONAL LINE ART

See ELECTRONIC FILES for CAD images
 (.DXF, .DWG, MS-DOS.EPS)



PART NUMBER

Description	Part No.
High Density 24-Port Patch Panel w/Wire Management Bar (1.75"H x 19"W)	49255-H24
High Density 48-Port Patch Panel w/Wire Management Bar (3.5"H x 19"W)	49255-H48

For Applications Engineering Support – Call 1-425-485-4288; in USA call 1-800-722-2082.
 Spec sheets and updates are also available at www.levitonvoicedata.com.



2222 – 222nd St. SE • Bothell, WA 98021 USA • Tel: 1-800-722-2082 / 1-425-485-4288 • Fax: 1-425-483-5270 • Int'l Fax: 1-425-485-9170 • GSA# GS-35F-4785G

