

# Definite Purpose Contactors 25 - 40 FLA 60 Hz 600VAC Max



### Class 42 - 2 & 3 pole

FLA	120V		240V			480V			600V		Non Inductive Amps	Poles	Catalog Number	Price
	Hp	LRA	Hp	LRA	Hp	LRA	Hp	LRA	Hp					
25	2	150	3	125	—	100	—	35	2	3	42AF15A*	\$ 90.00		
	—		5		7.5		3		7.5		42AF35A*	\$104.00		
30	2	180	5	150	—	120	—	40	2	3	42BF15A*	\$109.00		
	—		7.5		10		3		10		42BF35A*	\$116.00		
40	3	240	7.5	200	—	160	—	50	2	3	42CF15A*	\$122.00		
	—		10		15		3		15		42CF35A*	\$136.00		

### Class 42 Definite Purpose Contactor Features

- Compact Size
- Interchangeable Mounting on Durable Metal Back Plate
- Optional DIN Rail Mounting
- Weld-resistant Silver Cadmium Oxide Contacts
- Reinforced Thermoset Polyester Housing
- Quiet Operation Thanks to Cushioned Coil and Precision Fit Assembly
- Snap-On Electrical/Mechanical Interlocks
- Visual Contact Position Indication
- Power Terminations options:
  - Lugs (standard for 40A and above)
  - SEMS clamp
  - Binding Head screws (standard 25A-30A)
  - Quick Connects featuring One-Piece Durable Design (standard)
- Class F Coil Insulation
- Low VA Coils Standard for 25A – 40A
- Replacement Coils and Contact Kits see Page 30 and 31
- Meets:
  - ARI – 780
  - UL File E14900
  - CSA File LR6535
  - CE Approved thru 60A

### Ordering Instructions

Use complete catalog number. Replace the (\*) with letter from coil table

### Coil Voltages Table

60 Hz	50 Hz	Letter
24	24	J
110-120	110	F
200-208	—	D
208-240	190-220	G
277	240	L
440-480	380-440	H
550-600	550	E
110-120/ 220-240	—	A
200-240/ 440-480	—	C