

Pushbutton Units and Indicator Lights

30 mm Heavy Duty, Watertight/Oiltight, Class 52

• Revised •
03/20/2012

Legend plates for Class 51 and 52

Design

The 30 mm legend plates are approved for the use with both Class 51 and Class 52 devices. Automotive legend plates require 2 1/2" mounting centers. Plastic legend plates will have white letters engraved.

When ordering custom engraved legend plates, specify the required inscription text.

Selection and ordering data

Inscription	Large (1 7/16" x 2") Order No.	List Price \$	Automotive ^① (2 7/16" x 2 7/16") Order No.	List Price \$	Large Plastic ^② (1 7/16" x 2") Order No.	List Price \$	Automotive Plastic ^② (2 7/16" x 2 7/16") Order No.	List Price \$
"Blank (brushed aluminum)"	52NL02		52NA02		—	—	—	—
"Blank (red)"	52NL02R		52NA02R		52ND02R		52NE02R	
"Blank (Black)"	52NL02B		52NA02B		52ND02B		52NE02B	
Inscribed legend plates with large brushed aluminum background								
Close	52NL18		52NA18		—	—	—	—
Down	52NL10		52NA10		—	—	—	—
Emerg Stop	52NL16		52NA16		—	—	—	—
Emerg Stop (red)	52NL16R		52NA16R		—	—	—	—
Fast-Slow	52NL33		52NA33		—	—	—	—
Forward	52NL05		52NA05		—	—	—	—
For-Off-Rev	52NL38		52NA38		—	—	—	—
For-Rev	52NL31		52NA31		—	—	—	—
Hand-Off-Auto	52NL37		52NA37		—	—	—	—
High	52NL07		52NA07		—	—	—	—
High-Low	52NL30		52NA30		—	—	—	—
High-Off-Low	52NL44		52NA44		—	—	—	—
In	52NL21		52NA21		—	—	—	—
Jog	52NL13		52NA13		—	—	—	—
Jog-Forward	52NL24		52NA24		—	—	—	—
Jog-Reverse	52NL25		52NA25		—	—	—	—
Low	52NL08		52NA08		—	—	—	—
Lower	52NL20		52NA20		—	—	—	—
Man-Auto	52NL35		52NA35		—	—	—	—
Off	52NL12		52NA12		—	—	—	—
Off-On	52NL26		52NA26		—	—	—	—
On	52NL11		52NA11		—	—	—	—
On-Off-Auto	52NL40		52NA40		—	—	—	—
Open	52NL17		52NA17		—	—	—	—
Open-Close	52NL34		52NA34		—	—	—	—
Open-Off-Close	52NL41		52NA41		—	—	—	—
Out	52NL22		52NA22		—	—	—	—
Pull to Start Push to Stop	52NL47		52NA47		—	—	—	—
Raise	52NL19		52NA19		—	—	—	—
Raise-Lower	52NL36		52NA36		—	—	—	—
Reset	52NL14		52NA14		—	—	—	—
Reverse	52NL06		52NA06		—	—	—	—
Run	52NL23		52NA23		—	—	—	—
Run-Jog	52NL29		52NA29		—	—	—	—
Safe-Run	52NL27		52NA27		—	—	—	—
Slow-Off-Fast	52NL39		52NA39		—	—	—	—
Start	52NL03		52NA03		—	—	—	—
Start-Jog	52NL28		52NA28		—	—	—	—
Start-Stop	52NL32		52NA32		—	—	—	—
Stop	52NL04		52NA04		—	—	—	—
Stop (red)	52NL04R		52NA04R		—	—	—	—
Up	52NL09		52NA09		—	—	—	—
Up-Down	52NL49		52NA49		—	—	—	—
Up-Off-Down	52NL42		52NA42		—	—	—	—
Inscription plates with custom engraving								
"Custom engraved (brushed aluminum)"	52NL02E		52NA02E		—	—	—	—
"Custom engraved (red)"	52NL02RE		52NA02RE		52ND02RE		52NE02RE	
"Custom engraved (Black)"	52NL02BE		52NA02BE		52ND02BE		52NE02BE	
Max. number of rows	2		2		2		2	
Letter height	5/32"		1/4"		5/32"		1/4"	
Characters per row	14		16		14		16	

① Automotive requires 2 1/2" mounting centers

② White letters on plastic nameplate.