






ACCESSORY / SPARE PART ROUND,  
22MM/SQUARE,  
26X26MM: LED SUPER-BRIGHT LAMPS,  
BASE BA 9S BULB DIAMETER 10MM RATED VOLTAGE  
130V AC OPERATIONAL CURRENT MAX. 15 MA RED

#### General technical data:

<b>Product designation</b>		LED lamp, super bright
<b>Type of light source</b>		LED
<b>Color / of the light source</b>		red
<b>Mounting type</b>		BA 9s
<b>Product component</b>		
• series resistor		No
• diode		No
• lamp transformer		No
• Light source		Yes
<b>Type of voltage / for actuation</b>		AC/DC
<b>Operating voltage</b>		
• with AC / at 50 Hz / Rated value	V	130 ... 130
• with AC / at 60 Hz / Rated value	V	130 ... 130
• for DC / Rated value	V	90 ... 90
<b>Consumed current / for rated value of supply voltage / maximum</b>	mA	6
<b>Design of the electrical connection</b>		Miscellaneous
<b>Mounting type</b>		miscellaneous

#### Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates	other		
			<a href="#">Special Test Certificate</a>	<a href="#">Confirmation</a>	<a href="#">Environmental Confirmations</a>

**Further information:**

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrial-controls/mall>

**Cax online generator**

<http://www.siemens.com/cax>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3SB3901-1CD/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3SB3901-1CD](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SB3901-1CD)

**last change:**

Nov 17, 2014