






ACCESSORY / SPARE PART ROUND,
22MM/SQUARE,
26X26MM: LED SUPER-BRIGHT LAMPS,
BASE BA 9S BULB DIAMETER 10MM RATED VOLTAGE
130V AC-90V DC OPERATIONAL CURRENT MAX. 15 MA
GREEN

General technical data:		
Product designation		LED lamp, super bright
Type of light source		LED
Color / of the light source		green
Mounting type		BA 9s
Product component		
• series resistor		No
• diode		No
• lamp transformer		No
• Light source		Yes
Type of voltage / for actuation		AC/DC
Operating voltage		
• with AC / at 50 Hz / Rated value	V	130 ... 130
• with AC / at 60 Hz / Rated value	V	130 ... 130
• for DC / Rated value	V	90 ... 90
Consumed current / for rated value of supply voltage / maximum	mA	6
Design of the electrical connection		Miscellaneous
Mounting type		miscellaneous

Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates	other		
			Special Test Certificate	Confirmation	Environmental Confirmations

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)
<http://www.siemens.com/industrial-controls/mall>

Cax online generator
<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<http://support.automation.siemens.com/WW/view/en/3SB3901-1DD/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SB3901-1DD

last change: Nov 17, 2014