

# CADDY® CABLECAT J-Hook – CAT32



- Many sizes and designs available to attach to a variety of structures
- Cost effective alternative to expensive cable tray
- Galvanized finish on J-Hooks provide smoother cable pull and greater corrosion resistance
- cULus® Listed and complies with NEC® and TIA requirements for structured cabling systems



Part Number	CAT32
Material	Steel
Finish	Pre-galvanized
Diameter	2"
Cable Capacity, Cat 5e	80
Cable Capacity, Cat 6	50
Area	3.17 in <sup>2</sup>
Standard Packaging Quantity	60 pc
UPC	78285630014
UNSPSC	39131709
ETIM	EC000754
Approvals	cULus®

cULus is a registered certification mark of UL LLC. NEC is a registered trademark of, and National Electrical Code (NEC) standard is a copyright of the National Fire Protection Association, Inc.

#### WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at [www.erico.com](http://www.erico.com) and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright © 2013 ERICO International Corporation. All rights reserved.

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

