

# Hangers / Hanging Systems

## CADDY® SPEED LINK

### Features

- Reduces installation time
- Quickly installs as a stand-alone hanging system without drilling into the building structure
- Works with a variety of CADDY® Fasteners
- Meets the fire rating requirements of DIN 4102-2 for 30 minutes (for galvanized wire rope) and 90 minutes (for stainless steel wire rope) at 30 percent of rated load
- Reduces inventory, storage space and shipping costs
- Increases installation versatility
- Minimizes vibration and system wear and tear
- Improves installation aesthetics
- Unique steel locking device allows for adjustment both during and after installation



Fig. #1



Fig. #2



Fig. #3



Fig. #4



Fig. #5



Many ERICO® products are UL Listed.  
Please contact your ERICO representative for approval information.

# Hangers / Hanging Systems

Part Number	Fig. #	Wire Rope Diameter		Wire Rope Length (Y Length)		Working Load		Standard Packaging Quantity
		mm	in	m	ft	kg	lbs	
<b>HOOK</b>								
SLD2L1	1	2.0	0.079	1	3.3	45	100	100
SLD2L2	1	2.0	0.079	2	6.6	45	100	100
SLD2L3	1	2.0	0.079	3	9.9	45	100	100
SLD2L5	1	2.0	0.079	5	16.4	45	100	50
SLD2L7	1	2.0	0.079	7	22.9	45	100	25
SLD2L10	1	2.0	0.079	10	32.8	45	100	25
SLD3L1	1	3.0	0.118	1	3.3	90	200	100
SLD3L2	1	3.0	0.118	2	6.6	90	200	100
SLD3L3	1	3.0	0.118	3	9.9	90	200	50
SLD3L5	1	3.0	0.118	5	16.4	90	200	50
SLD3L7	1	3.0	0.118	7	22.9	90	200	25
SLD3L10	1	3.0	0.118	10	32.8	90	200	25
<b>HOOK (Stainless Steel)</b>								
SLD3L2SS	1	3.0	0.118	2	6.6	90	200	100
SLD3L3SS	1	3.0	0.118	3	9.9	90	200	50
<b>Y-TOGGLE</b>								
SLD2Y300	2	2.0	0.079	(300 mm)	(11.8 in)	45	100	20
SLD2Y500	2	2.0	0.079	(500 mm)	(19.6 in)	45	100	20
<b>INTEGRAL Y-TOGGLE</b>								
SLD2Y300L2	3	2.0	0.079	2 (300 mm)	6.6 (11.8 in)	45	100	20
SLD2Y300L3	3	2.0	0.079	3 (300 mm)	9.9 (11.8 in)	45	100	20
SLD2Y300L5	3	2.0	0.079	5 (300 mm)	16.4 (11.8 in)	45	100	20
SLD2Y300L7	3	2.0	0.079	7 (300 mm)	22.9 (11.8 in)	45	100	20
SLD2Y300L10	3	2.0	0.079	10 (300 mm)	32.8 (11.8 in)	45	100	10
SLD2Y500L3	3	2.0	0.079	3 (500 mm)	9.9 (19.6 in)	45	100	20
<b>Y-HOOK</b>								
SLD2YH500	4	2.0	0.079	(500 mm)	(19.6 in)	45	100	10
SLD2YH800	4	2.0	0.079	(800 mm)	(31.4 in)	45	100	10
SLD3YH500	4	3.0	0.118	(500 mm)	(19.6 in)	90	200	10
SLD3YH800	4	3.0	0.118	(800 mm)	(31.4 in)	90	200	20
<b>INTEGRAL Y-HOOK</b>								
SLD2YH500L2	5	2.0	0.079	2 (500 mm)	6.6 (19.6 in)	45	100	20
SLD2YH500L3	5	2.0	0.079	3 (500 mm)	9.9 (19.6 in)	45	100	20
SLD2YH500L7	5	2.0	0.079	7 (500 mm)	22.9 (19.6 in)	45	100	20
<b>2-PACKS - INTEGRAL Y-HOOK</b>								
SLD2YH500L2TP	5	2.0	0.079	2 (500 mm)	6.6 (19.6 in)	45	100	1
SLD2YH500L3TP	5	2.0	0.079	3 (500 mm)	9.9 (19.6 in)	45	100	1
SLD2YH500L7TP	5	2.0	0.079	7 (500 mm)	22.9 (19.6 in)	45	100	1
<b>INDIVIDUALLY PACKAGED HOOK</b>								
SLD2L1BP	1	2.0	0.079	1	3.3	45	100	1
SLD2L2BP	1	2.0	0.079	2	6.6	45	100	1
SLD2L3BP	1	2.0	0.079	3	9.9	45	100	1
SLD2L5BP	1	2.0	0.079	5	16.4	45	100	1
SLD2L10BP	1	2.0	0.079	10	32.8	45	100	1
SLD3L1BP	1	3.0	0.118	1	3.3	90	200	1
SLD3L2BP	1	3.0	0.118	2	6.6	90	200	1
SLD3L3BP	1	3.0	0.118	3	9.9	90	200	1
SLD3L5BP	1	3.0	0.118	5	16.4	90	200	1
SLD3L10BP	1	3.0	0.118	10	32.8	90	200	1