



WireTwist™ Wire Connectors



WireTwist™

- “Stayset spring”
- CSA certified and UL listed for solid and stranded wire
- Fast make-up for easier installation
- Heavy gauge outer shell for superior dielectric performance
- Double plated spring process for superior corrosion resistance
- Wide wire range combinations
- Designed to appeal to users of wingless connectors



WireTwist™ Wire Connectors



- “Stayset spring” to ensure each and every connector is usable resulting in better cost efficiency.
- CSA Certified and UL Listed as a pressure type connector for 600V maximum building wire, and 1000V maximum for in signage/fixture applications
- Superior corrosion resistance
- Designed to appeal to users of wingless connectors



Model	Colour	Wire Combination Range	Wire Combination Range (mm)	Quantity	Cat. No.
C3	Orange	600V No. 18 thru 14 AWG Min. 2 No. 18 Max. 3 No. 14	600V 1.02mm DIA to 1.63mm DIA Min. 1.64mm ² Max. 6.26mm ²	C-Pak of 100	30-0C3
				Flip-Tub of 500	30-3C3
				Flip-Tub of 1,000	30-4C3
				Keg of 10,000	30-6C3
				Barrel of 45,000	30-8C3
C4	Yellow	600V No. 18 thru 10 AWG Min. 1 No. 14 with 2 No. 18 Max. 1 No. 10 with 2 No. 14	600V .62mm DIA to 2.59mm DIA Min. 3.74mm ² Max. 9.42mm ²	C-Pak of 100	30-0C4
				Flip-Tub of 500	30-3C4
				Flip-Tub of 1,000	30-4C4
				Keg of 10,000	30-6C4
				Barrel of 25,000	30-8C4
C6	Red	600V No. 18 thru 14 AWG Min. 2 No. 16 with 2 No. 18 Max. 3 No. 10	600V 1.02mm DIA to 3.26mm DIA Min. 4.25mm ² Max. 15.78mm ²	C-Pak of 100	30-0C6
				Flip-Tub of 200	30-1C6
				Flip-Tub of 500	30-3C6
				Keg of 8,000	30-6C6

Wire Combinations								
	3#22	2#18	2#16w/2#18	1#14w/2#18	1#14w/4#12	3#14	1#10w/2#14	3#10
C3		[Orange bar]						
C4				[Yellow bar]				
C6			[Red bar]					