



# Canadian Products Supplement



# Can-TWIST™ Wire Connectors

- Exceptional wire-range capacity, handles wire combinations from 22 to 8 AWG solid and/or stranded wires
- Spring threads are heat-set making them more reliable
- Flexible walls show when wires are firmly connected
- Extended skirt length provides over-strip protection
- Easily removed for repeat usage
- Smaller size makes it easier to work in tight spaces
- Wide mouth and square springs deliver quick pick-up
- Swept wings provide added gripping power
- Easier to twist. Only a few turns are necessary to achieve torque
- CSA 22.2 #188 Certified



Can-Twist  
105°C/221°F



Can-Twist Extrême  
High-Temp  
150°C/302°F

## CANADA'S BEST SELLING CONNECTOR

MODEL	COLOUR	WIRE COMBINATION RANGE	WIRE COMBINATION (MM)	QUANTITY	CAT. NO.
<b>Can-Twist 007</b>	Blue	600V No. 22 thru 8 Awg Min. 3 No. 22 Max 3 No. 10	600V .64mm DIA to 3.26mm DIA Min .97mm <sup>2</sup> Max. 15.78mm <sup>2</sup>	Pack of 15	30-157
				C-Pak of 100	30-207
				Jar of 175	30-107J
				Jar of 475	30-307J
				Bag of 500	30-607
				Jar of 1,000	30-707J
				Stubby of 7,500	30-817
				Barrel of 25,000	30-807
<b>Can-Twist Extrême 007XT High-Temp</b>	Black	600V No. 22 thru 8 Awg Min. 3 No. 22 Max 4 No. 11 (solid)	600V .64mm DIA to 3.26mm DIA Min .97mm <sup>2</sup> Max. 13.24mm <sup>2</sup>	Pack of 15	30-157XT
				Jar of 175	30-107XTJ
				Jar of 475	30-307XTJ
				Stubby of 7,500	30-817
				Barrel of 25,000	30-807XTJ

Can-Twist 007	3 # 22 1,920 (.97 mm <sup>2</sup> )	3 # 14 12,330 (6.24 mm <sup>2</sup> )	3 # 10 31,140 (15.78 mm <sup>2</sup> )
Combination CIR MIL Area			
Can-Twist 007XT	3 # 22 1,920 (.97 mm <sup>2</sup> )	3 # 14 12,330 (6.24 mm <sup>2</sup> )	4 # 12 26,120 (13.44 mm <sup>2</sup> )

Dimensions for Model Can-Twist 007/Can-Twist Extrême 007XT

DIMENSIONS	A	B	C	D	E
Inches	1/4	7/16	3/4	7/16	1 1/8
mm	7	11.5	19	11.5	29

Cu/Cu Only

**Ask about volume pricing**



## Wire Connectors



- “Stayset spring” to ensure each and every connector is usable resulting in better cost efficiency
- CSA Certified and UL Listed as a pressure type connector for 600V maximum building wire, and 1000V maximum for in signage/fixture applications
- Superior corrosion resistance
- Designed to appeal to users of wingless connectors



Model	Colour	Wire Combination Range	Wire Combination Range (mm)	Quantity	Cat. No.
C3	Orange	600V No. 18 thru 14 AWG Min. 2 No. 18 Max. 3 No. 14	600V 1.02mm DIA to 1.63mm DIA Min. 1.64mm <sup>2</sup> Max. 6.26mm <sup>2</sup>	C-Pak of 100	30-0C3
				Flip-Tub of 500	30-3C3
				Flip-Tub of 1,000	30-4C3
				Keg of 10,000	30-6C3
				Barrel of 45,000	30-8C3
C4	Yellow	600V No. 18 thru 10 AWG Min. 1 No. 14 with 2 No. 18 Max. 1 No. 10 with 2 No. 14	600V .62mm DIA to 2.59mm DIA Min. 3.74mm <sup>2</sup> Max. 9.42mm <sup>2</sup>	C-Pak of 100	30-0C4
				Flip-Tub of 500	30-3C4
				Flip-Tub of 1,000	30-4C4
				Keg of 10,000	30-6C4
				Barrel of 25,000	30-8C4
C6	Red	600V No. 18 thru 14 AWG Min. 2 No. 16 with 2 No. 18 Max. 3 No. 10	600V 1.02mm DIA to 3.26mm DIA Min. 4.25mm <sup>2</sup> Max. 15.78mm <sup>2</sup>	C-Pak of 100	30-0C6
				Flip-Tub of 200	30-1C6
				Flip-Tub of 500	30-3C6
				Keg of 8,000	30-6C6
				Barrel of 20,000	30-8C6

## Canadian Connector Kit

#30-2088

**NEW**

- A variety of connectors to fit a large range of wire sizes No. 6 AWG - 26 AWG
- Great for Servicing Technicians
- Convenient and durable carrying case

