


## Slotted Heavy-Duty w/Keystone Tip



- Larger shank for heavy-duty applications
- Identification mark on ends
- Vapor-blasted tip prevents plate chipping
- Precision ground tip provides secure fit in screw slot
- Square-shank models offer wrench-assisted turning
- Tough, chrome vanadium steel shank
- Cushioned rubber grips

Square Shank	Blade Length	Total Length	Cat. No.
1/4 in. Shank and tip	4 in.	8-3/8 in.	<b>35-154</b>
5/16 in. Shank and tip	6 in.	11 in.	<b>35-156</b>
5/16 in. Shank and tip	8 in.	13 in.	<b>35-158</b>

Round Shank	Blade Length	Total Length	Cat. No.
1/4 in. Shank and tip	1 in.	3-3/8 in.	<b>35-161</b>
1/4 in. Shank and tip	4 in.	8-3/8 in.	<b>35-164</b>
5/16 in. Shank and tip	6 in.	11 in.	<b>35-166</b>
5/16 in. Shank and tip	8 in.	13 in.	<b>35-168</b>

## Slotted Heavy-Duty w/Cabinet Tip



- Large diameter shank for tough applications
- Identification marks on ends
- Vapor-blasted tip prevents plate chipping
- Precision ground tip provides secure fit in screw slot
- Nickel-chrome plating for corrosion resistance
- Tough, chrome vanadium steel shanks
- Cushioned rubber grip

Description	Blade Length	Total Length	Cat. No.
1/4 in. Shank and tip	4 in.	8-3/8 in.	<b>35-150</b>
1/4 in. Shank and tip	6 in.	10-3/8 in.	<b>35-151</b>
1/4 in. Shank and tip	8 in.	12-3/8 in.	<b>35-152</b>
1/4 in. Shank and tip	10 in.	14-3/8 in.	<b>35-153</b>


## Slotted Cabinet Tip



- Vapor-blasted tip prevents plate chipping
- Identification mark on ends
- Precision ground tip provides secure fit in screw slot
- Nickel-chrome plating for corrosion resistance
- Tough, chrome vanadium steel shank
- Cushioned rubber grip

Description	Blade Length	Total Length	Cat. No.
3/16 in. Shank and tip	3 in.	6-3/4 in.	<b>35-183</b>
3/16 in. Shank and tip	4 in.	7-3/4 in.	<b>35-184</b>
3/16 in. Shank and tip	6 in.	9-3/4 in.	<b>35-186</b>
3/16 in. Shank and tip	8 in.	11-3/4 in.	<b>35-188</b>
3/16 in. Shank and tip	10 in.	13-3/4 in.	<b>35-190</b>

## Phillips



- Vapor-blasted tip prevents plate chipping
- Identification mark on ends
- Nickel-chrome plating for corrosion resistance
- Tough, chrome vanadium steel shank
- Cushioned rubber grip

Description	Blade Length	Total Length	Cat. No.
#1 Phillips	3 in.	6-3/4 in.	<b>35-193</b>
#2 Phillips	1 in.	3-3/8 in.	<b>35-191</b>
#2 Phillips	4 in.	8-3/8 in.	<b>35-194</b>
#2 Phillips	6 in.	10-3/8 in.	<b>35-195</b>
#3 Phillips	6 in.	11 in.	<b>35-196</b>