

Write-On Marker Cards

- Use for developing personal identification systems
- Cloth write-on surface
- Accepts most writing instruments



Marker Size (Inches)	Markers per card	Cat. No.
5/8 x 1-1/2	14	44-753

Marking Pens

- Fast-drying, permanent ink will not smear
- Use on write-on marker cards and write-on cable-tie marker plates
- Color-coded in red or black



Description	Cat. No.
Marking Pen w/black ink	41-697
Marking Pen w/red ink	41-698

Wire Marker Dispensers

- Convenient pocket-size case (3 in. x 6 in.) holds 10 wire marker rolls
- Dispenser tab holds tapes firmly in place — allows removal of proper tape length without waste
- Flip top for easy access and refill
- Built-in hook for hanging from belt or tool pouch
- High-quality adhesive and 3 mil. thickness provide long-lasting, low-profile application
- Each plastic reel holds 8 ft. of polyester tape



Specifications:

Temperature Range: -40°F to 180°F (-40°C to 82°C)
Adhesion: 25 oz./in. width ultimate

Description	Cat. No.
Dispenser w/0 through 9 legend rolls	42-301
Refill pack with 1 each of 0-9 legend rolls	42-399

Wire Marker Cards

- Use for positive identification and keying of wires, terminal blocks, etc.
- Convenient pocket-size cards
- Bold, easy-to-read black characters
- Self-sticking on wire and cable
- Polyester film over laminate/cloth construction for long-term durability
- Resists abrasion, moisture, dirt and oil
- Individual markers measure approximately 1/4 in. x 1-1/2 in.

Specifications:

Temperature Range: -40°F to 180°F (-40°C to 82°C); Adhesion: 45 oz./in. width ultimate



Legend	Markers per legend	Markers per card	Cat. No.
0-9 (Repeated)	3	30	43-953
A-Z	1	26	43-960

Voltage and Conduit Markers

Large:

1 marker per card
2-1/4 in. x 9 in. each w/1-3/4 in. type

Medium:

4 markers per card
1-1/8 in. x 4-1/2 in. each w/3/4 in. type

Small:

18 markers per card
2-1/4 in. x 1/2 in. each w/5/16 in. type



- Identify junction boxes, switches, circuit breakers, raceways, pipe and fuse boxes
- Non-conductive for user safety
- High-adhesion properties with easy removability
- Vinyl-impregnated cloth construction provides long-lasting durability
- Resist abrasion, moisture, dirt and oil
- Non-smear, black legend on bright orange background for high visibility

Specifications:

Temperature Range: -40°F to 180°F (-40°C to 82°C)
Adhesion: 45 oz./in. width ultimate

Legend	Large Cat. No.	Medium Cat. No.	Small Cat. No.
120/208V	44-295	44-296	—
277/480V	44-298	44-299	—
120V	—	44-353	—
208V	—	44-355	—
240V	—	44-358	—
277V	—	—	44-410
480V	44-314	44-364	—
DANGER	44-289	—	—
HIGH VOLTAGE	44-292	—	—