

Can-Twist Wire Connectors

The new Canadian Standard in wire connectors, Can-Twist is the only one you'll ever need.



- Exceptional wire-range capacity handles wire combinations from 22 to 8 AWG solid and/or stranded wires
- Spring threads are heat-set making them more reliable
- Flexible walls show when wires are firmly connected
- · Easily removed for repeat usage
- Extended skirt length provides over-strip protection
- Smaller size makes it easier to work in tight spaces
- Wide mouth and square springs deliver quick pick-up
- Swept wings provide added gripping power
- Easier to twist. Only a few turns are necessary to achieve torque

Can-Twist

105°C/ 221°F

Can-Twist XT

150°C/302°F

• CSA 22.2#188 Certified



Can-Twist 007	3#22	3#14	3#10	
	1,920 (.97mm²)	12,330 (6.24mm²)	31,140 (15.78mm²)	
Combination CIR MIL	Area			
3#22		3#14	4#12	
Can-Twist 007XT 1,920 (.97mm²)		12,330 (6.24mm²)	26,120 (13.44mm²)	

Dimensions for Model Can-Twist 007/007XT

DIMENSIONS	Α	В	С	D	E
Inches	1/4	7/16	3/4	7/16	1 1/8
mm	7	11.5	19	11.5	29

Cu/Cu Only



P-1963

12/05