



# DATA COMM / NETWORKS

## Crimpmaster™ Crimp Tools & Die Sets

High quality ratchet-type crimp tool for electricians, contractors and installers who require guaranteed repeatability of good mechanical and electrical connections.

Dies change quickly and easily with a screwdriver. Interchangeable dies provide versatility in a single tool.



Description	Cat. No.
Crimpmaster™ Crimp Frame Tool	30-506

### Also available in these kits:

33-400



33-917



**30-556**  
RJ-11 Crimp Tool for two, four or six-position modular plugs  
**Tool w/die N/A**



**30-559**  
RJ-45 Eight-position Crimp Tool for keyed or non-keyed modular plugs  
**Tool w/die 30-522**



**30-560**  
RJ-45 Eight-position Crimp Tool for AMP® RJ-45 modular plugs  
**Tool w/die 30-521**



**30-570**  
RG-6, RG-174, Belden® Type RG-8281 cables (Hex. 0.324 (8.23mm), 0.178 (4.52mm), 0.068 (1.73mm))  
**Tool w/die N/A**



**30-573**  
Cambridge CP-88, CP-89 BNC/TNC coax connectors with RG-58, RG-59/RG-62 AU cables (Hex 0.305 (7.75mm), 0.068 (1.73mm), 0.228 (5.79mm))  
**Tool w/die 30-481**



**30-576**  
RG-174, Mini 59 BNC/TNC Connectors (Hex. 0.178 (4.52mm), 0.128 (3.25mm), 0.068 (1.73mm))



**30-577**  
N-Series and RG-8/11 Connectors (Hex. 0.429 (10.90mm), 0.100 (2.54mm), 0.080 (2.03mm))  
**Tool w/die 30-482**



**30-578**  
RG-59, RG-6, and 8281 50 and 75 OHM cables (Hex, 0.324 (8.23mm), 0.255 (6.48mm), 0.068 (1.73mm), 0.042 (1.07mm))  
**Tool w/die 30-483**



**30-581**  
RG-58, RG-59/62, BNC/TNC Coax Connectors (Hex, 0.255 (6.48mm), 0.213 (5.41mm), 0.068 (1.73mm))  
**Tool w/die 30-502**



**30-582**  
F-type CATV RG-59, RG-6 Connectors (Hex, 0.350 (8.89mm), 0.320 (8.13mm), 0.255 (6.48mm))  
**Tool w/die 30-503**



**30-587**  
RG-58, RG-174 and G-8218 for both 50 and 75 ohm cables (Hex 0.213 (5.41mm), 0.178 (4.52mm), 0.068 (1.73mm), 0.042 (1.07mm))  
**Tool w/die N/A**



**30-591**  
Plenum and Non-Plenum Thinwire Cables RG-58 and 59 (Hex, 0.213 (5.41mm), 0.190 (4.83mm), 0.068 (1.73mm), 0.042 (1.07mm))  
**Tool w/die N/A**



**30-593**  
Mini UHF and BNC/TNC 5 cavity (Hex, 0.052 (1.32mm), 0.068 (1.73mm), 0.100 (2.54mm), 0.213 (5.41mm), 0.255 (6.48mm))  
**Tool w/die N/A**



**30-572**  
16-26 AWG (.131mm<sup>2</sup> - .128mm<sup>2</sup>) miniature insulated rings, spade and butt splices  
**Tool w/die N/A**



**30-579**  
22-10 AWG (.324mm<sup>2</sup> - 5.261mm<sup>2</sup>) insulated terminals/color coded nests  
**Tool w/die 30-500**



**30-580**  
22-8 AWG (.3mm<sup>2</sup> - 8mm<sup>2</sup>) non-insulated terminals  
**Tool w/die N/A**



**30-586**  
22-12 AWG (.324mm<sup>2</sup> - 3.31mm<sup>2</sup>) Non Insulated Open Barrel Connectors, Commercial Type  
**Tool w/die N/A**



**30-594**  
Fully Insulated quick disconnect terminals with thinner wire barrels 22-10 AWG (.324mm<sup>2</sup> - 5.261mm<sup>2</sup>)  
**Tool w/die N/A**



**30-599**  
30-18 AWG (.205mm<sup>2</sup> - 2.08mm<sup>2</sup>) Open Barrel Pins and Sockets  
**Tool w/die N/A**



**30-479 (Tool w/die)**  
For insulated terminals, 22-10 AWG with built-in locator