

T®-Stripper Wire Strippers

- Form-ground, knife-type blades for accurate, easy stripping without nicking insulation
- Built-in wire cutter and looping holes
- Convenient plier nose for extra gripping strength



- Spring-loaded automatic opening
- Corrosion-resistant, black oxide finish
- Tough steel construction

Description	Solid	Stranded	Cat. No.
T®-5 T®-Stripper Wire Stripper	10-18	12-20	45-120
T®-6 T®-Stripper Wire Stripper	14-24	16-26	45-121
T®-7 T®-Stripper Wire Stripper	22-30	24-32	45-125
T®-8 T®-Stripper Wire Stripper	6-14	8-16	45-124
T®-Stripper Wire Stripper – Metric	0.75-6mm ²		45-120-341
T®-Stripper Wire Stripper – Metric	0.5-4mm ²		45-125-341

NM Cable T®-Stripper Wire Strippers

- Easy, one-step stripping of outer jacket of NM cable — no slitting required
- Versatility to strip, cut and loop conductor wires with precision and ease
- Stripping holes for12 or 14 AWG solid wire
- Locking pawl for safe storage

Description	Cat. No.
14/2 NM Cable T®-Stripper Wire Stripper	45-248
12/2 NM Cable T®-Stripper Wire Stripper	45-249
Reflex™ Super 12/2 & 14/2 NM Cable T®-Stripper Wire Stripper	45-621
Reflex™ Super 12/3 & 14/3 Cable T®-Stripper Wire Stripper	45-622

NM Cable Dual-Hole T®-Stripper Wire Stripper

- Stripping holes for stripping two 12 AWG or two 14 AWG wires simultaneously
- Ability to strip both conductor wires of NM cable at one time

Description	Wire Range	Cat. No.
Premium T®-14 T®-Stripper Wire Stripper	12 or 14 AWG solid	45-247

Romex® is a registered trademark of Southwire.

Super T®-Stripper Wire Strippers

- 6-32 and 8-32 self-chasing screwcutting holes (not available on metric stripper)
- Curved, cushion-grip handles for ergonomic comfort
- Locking pawl to keep stripper in closed position
- Built-in wire cutter and looping holes
- Convenient plier nose for extra gripping strength
- Laser-etched wire gauge for easy-to-read visibility
- Spring-loaded automatic opening
- Tough steel construction, corrosion-resistant, black oxide finish

Description	Solid	Stranded	Cat. No.
Super T®-5 T®-Stripper Wire Stripper	8-16	10-18	45-315
Super T®-8 T®-Stripper Wire Stripper	6-14	8-16	45-318
Super T®-Stripper Wire Stripper – Metric	0.5-4mm ²		45-310-341
Super T®-Stripper Wire Stripper – Metric	0.75-6mm ²		45-315-341
Super T®-Stripper Wire Stripper – Metric	0.5-4mm ²		45-317-341

Lil' Ripper Stripper™

- Rips Romex® outer jacket cleanly and quickly
- Clips outer sheathing to remove excess Romex® jacket
- Strips inner conduit wires
- Looping holes loop wire for screw-on connections
- Twist-Assist™ tightens most popular sizes of winged twist-on connectors
- Injection molded elastomer grip provides a comfortable, slip resistant grip
- Strip length measuring scale allows for quick and easy measurements
- Conveniently fits in your pocket

Description	Cat. No.
Lil' Ripper Stripper™	45-025

Reflex™ Super T®-Stripper Wire Strippers

- 6/32 and 8/32 self-chasing screw-cutting holes
- Locking pawl for safe storage
- Ergonomic design for maximum comfort
- Curved handles reduce wrist fatigue
- Sleeves that extend to stripping head to cushion thumb and fingers
- Textured sleeves with extra cushioning for added comfort

Description	Solid	Stranded	Cat. No.
Reflex™ Super 12/2 & 14/2 NM Cable T®-Stripper Wire Stripper	12-2 and 14-2	_	45-621
Reflex™ Super 12/3 & 14/3 NM Cable T®-Stripper Wire Stripper	12-3 and 14-3	_	45-622