



# TEST & MEASUREMENT

## Clamp Meter Selection Guide

CLAMP METER SELECTION GUIDE	700 Series		740 Series		760 Series		770 Series	
	61-702	61-704	61-744	61-746	61-763	61-765	61-773	61-775
<b>MEASUREMENT FUNCTIONS</b>								
AC Voltage	•	•	•	•	•	•	•	•
DC Voltage	•	•	•	•	•	•	•	•
AC Current	•	•	•	•	•	•	•	•
DC Current						•		•
Resistance	•	•	•	•	•	•	•	•
Audible Continuity	•	•	•	•	•	•	•	•
Diode Test	•	•						
Capacitance	•	•			•	•	•	•
Frequency					•	•	•	•
<b>FEATURES</b>								
Display Type (Digital)	D	D	D	D	D	D	D	D
AC Current Capacity	200	200	600	600	660	660	1000	1000
DC Current Capacity						660		1000
True RMS		•		•	•	•	•	•
Auto Ranging	•	•						
Auto/Manual Ranging			•	•	•	•	•	•
Data Hold	•		•	•	•	•	•	•
Max Hold	•	•						
Peak Hold					•	•	•	•
Min/Max					•	•	•	•
DCA Zero					•	•	•	•
Auto Power Off	•	•	•	•	•	•	•	•
Non-Contact Voltage Indication	•	•	•	•				
Harmonics Indicator	•	•						
Vibration Mode	•	•						
Backlight		•			•	•	•	•
Low Battery Indication	•	•	•	•	•	•	•	•
High Voltage Warning	•	•			•	•	•	•
Overload Protection on all Ranges	•	•	•	•	•	•	•	•
Conductor Size – Inches (mm)	1.3" (33)	1.3" (33)	1.5" (38)	1.5" (38)	1.4" (36)	1.4" (36)	2.0" (51)	2.0" (51)
Warranty (years)	2	2	2	2	2	2	2	2
<b>CERTIFICATIONS</b>								
UL 61010 Listed	•	•	•	•	•	•	•	•
CAT III, 100V/CAT IV 600V	III	III	III	III	IV	IV	IV	IV
CE	•	•	•	•	•	•	•	•



CLAMP METERS

# TightSight® Clamp Meters 1000 & 660 Amp

- TightSight® bottom display
  - Tapered jaws with hook tip
  - Measures AC current
  - True RMS
  - AC/DC Voltage
  - Capacitance
  - Audible continuity
  - Frequency via clamp head or test leads
  - Resistance
  - High frequency rejection\*
  - Peak hold
  - Max/min hold
  - Data hold
  - Selectable audible and visual voltage alerts on AC/DC voltage functions
  - Selectable auto power off
  - Backlit display
  - Low battery indicator
  - 2-year warranty
- \*Reads accurately on noisy electrical circuits.



1000A Clamp  
(61-773)



Exclusive TightSight®  
Display



660A Clamp  
(61-763)

Description	Cat. No.
1000AAC Clamp Meter	61-773
1000A AC/DC Clamp Meter	61-775
660AAC Clamp Meter	61-763
660A AC/DC Clamp Meter	61-765

Includes: Carrying Case and Test Leads w/Alligator Clip.

## Specifications

	Range & Resolution				Accuracy
	61-773	61-775	61-763	61-765	
AC Current	0.0-999.9A		0.0-660.0A		2.0%
DC Current	—	0.0-999.9A	—	0.0-660.0A	2.0%
AC Voltage	0.0-750.0V				1.0%
DC Voltage	0.0-999.9V				1.0%
Resistance	0.0-999.9Ω				1.5%
Capacitance	0.0-999.9μF				5.0%
Continuity	0.0-999.9Ω				Audible @ <30Ω
Frequency	20.0-400.0Hz				0.5%
Jaw Size	2" (51mm)		1.42" (36mm)		—