

VJ SERIES | RVJ, CVJ & CUSTOM WINDOWS

RVJ Raised Cover Units

The raised cover option provided by the RVJ series allows greater enclosure depth.

All features and accessory options of the standard VJ series also apply to the RVJ series.


CVJ Clearview Bonded Window Cover Units

CVJ enclosures feature clearview bonded windows on the cover for total window access. The polycarbonate window is very durable, and CVJ construction maintains NEMA 4X integrity.

| Part Number* | Outside Dimension | | | Inside Dimension | | | Weight |
|--------------|-------------------|-------|-------|------------------|-------|-------|--------|
| | H | W | D | h | w | d | |
| RVJ1008* | 11.31 | 9.31 | 6.93 | 10.00 | 8.00 | 6.18 | 4.90 |
| RVJ1210* | 13.31 | 11.31 | 7.09 | 12.00 | 10.00 | 6.34 | 6.50 |
| RVJ1412* | 15.32 | 13.30 | 8.19 | 14.00 | 12.00 | 7.31 | 8.80 |
| RVJ1614* | 17.31 | 15.31 | 8.19 | 16.00 | 14.00 | 7.37 | 10.80 |
| RVJ1816* | 19.31 | 17.31 | 11.08 | 18.00 | 16.00 | 10.23 | 14.25 |

* COMPLETE YOUR PART NUMBER WITH SUFFIX FROM THE BOX BELOW

Also available with bonded window (RVJB...).

| Part Number* | Outside Dimension | | | Inside Dimension | | | Weight |
|--------------|-------------------|-------|------|------------------|-------|------|--------|
| | H | W | D | h | w | d | |
| CVJ606* | 7.31 | 7.31 | 4.96 | 6.00 | 6.00 | 4.21 | 2.80 |
| CVJ806* | 9.31 | 7.31 | 4.96 | 8.00 | 6.00 | 4.21 | 3.80 |
| CVJ1008* | 11.31 | 9.31 | 5.43 | 10.00 | 8.00 | 4.69 | 4.80 |
| CVJ1210* | 13.31 | 11.31 | 5.59 | 12.00 | 10.00 | 4.84 | 6.30 |
| CVJ1412* | 15.32 | 13.30 | 6.70 | 14.00 | 12.00 | 5.82 | 8.60 |
| CVJ1614* | 17.31 | 15.31 | 6.69 | 16.00 | 14.00 | 5.82 | 10.60 |
| CVJ1816* | 19.31 | 17.31 | 9.57 | 18.00 | 16.00 | 8.69 | 14.00 |

* COMPLETE YOUR PART NUMBER WITH SUFFIX FROM THE BOX BELOW

NOTE: CVJ enclosures are not available in RVJ (raised cover) format. UL listed for Type 3, 3R, 4, 4X, 12, 13.



Gasketed windows not UL listed.



Bonded windows UL listed for Type 3, 3R, 4, 4X, 12, 13.

| Part Number* | Max Window | |
|--------------|------------|-------|
| | H | W |
| VJ(B/G)606* | 4.00 | 4.00 |
| VJ(B/G)806* | 6.00 | 4.00 |
| VJ(B/G)1008* | 8.00 | 6.00 |
| VJ(B/G)1210* | 10.00 | 8.00 |
| VJ(B/G)1412* | 12.00 | 10.00 |
| VJ(B/G)1614* | 14.00 | 12.00 |
| VJ(B/G)1816* | 16.00 | 14.00 |

Custom Windows

Custom polycarbonate bonded (B) or gasketed (G) style windows are available. Contact your sales representative to discuss specific requirements.

* COMPLETE YOUR PART NUMBER WITH SUFFIX FROM THE BOX AT RIGHT

PART NUMBER SUFFIXES

| | |
|---------------|---|
| W | screw-type cover |
| HW | stainless steel hinge w/screw-type cover |
| HWLL1 | stainless steel hinge w/1 twist latch (available for 606 through 1008 units) |
| HWLL2 | stainless steel hinge w/2 twist latches (available for 1210 through 1816 units) |
| HWPL1 | stainless steel hinge w/1 padlockable quick release latch (available for 606 through 1008 units) |
| HWPL2 | stainless steel hinge w/2 padlockable quick release latches (available for 1210 through 1816 units) |
| NHW | non-metallic hinge w/screw-type cover |
| NHWLL1 | non-metallic hinge w/1 twist latch (available for 606 through 1008 units) |
| NHWLL2 | non-metallic hinge w/2 twist latches (available for 1210 through 1816 units) |
| NHWPL1 | non-metallic hinge w/1 padlockable quick release latch (available for 606 through 1008 units) |
| NHWPL2 | non-metallic hinge w/2 padlockable quick release latches (available for 1210 through 1816 units) |