

# In-Line Fuse Holders SFRT, SFRB, SFRG, FSFE, SFRU

## SFRT

- Twist-lock
- In-line fuse holders for FSFE fuses.
- Used at 32V or less with fuses rated up to 20A when proper spring for fuse size is installed.



## SFRB

- Bayonet knob
- In-line fuse holders for FSFE fuses.
- Used at 32V or less with fuses rated up to 20A when proper spring for fuse size is installed.



## Standard Fuse Ampere Ratings

Catalog Number*	Fuse Installed
SFRT4	FSFE4
SFRT6	FSFE6
SFRT7-1/2	FSFE7-1/2
SFRT9	FSFE9
SFRT14	FSFE14
SFRT20	FSFE20

\*Includes FSFE fuse

## Standard Fuse Ampere Ratings

Catalog Number*	Fuse Installed
SFRB4	FSFE4
SFRB6	FSFE6
SFRB7-1/2	FSFE7-1/2
SFRB9	FSFE9
SFRB14	FSFE14
SFRB20	FSFE20

\*Includes FSFE fuse

## SFRG

- In-line fuse holder for 5 x 20mm fuses.
- Max. current rating for 5x20mm fuses - 10A @ 32V



## FSFE

- Glass body
- Fast-acting

4A through 30A, 32VAC/DC - UL Listed



## SFRU

Universal in-line fuse holder - supplied with 15" loop of #14 AWG red vinyl insulated wire frame and three springs in different lengths to accommodate FSFE size fuses.



## Standard Fuse Ampere Ratings

Catalog Number	Ampere Rating	Volts	Fuse Length
FSFE4	4A	32V	5/8"
FSFE6	6A	32V	3/4"
FSFE7-1/2	7-1/2A	32V	7/8"
FSFE9	9A	32V	7/8"
FSFE14	14A	32V	1-1/16"
FSFE20	20A	32V	1-1/4"
FSFE30	30A	32V	1-7/16"