

Pilot and Signaling Devices

Heavy-Duty 30.5 mm Watertight/Oiltight Push Buttons

CR104P

Standard

Non-Illuminated

600 Volts Maximum AC/DC

10 Amperes Continuous

Suitable for use in NEMA Type 1, 3, 3R, 4, 4X, 12, and 13 applications when mounted in enclosures rated for those same applications. For some NEMA Type 4X applications, protective caps will improve corrosion resistance.

Extended Button - Momentary Operator

Contact Configuration	Color	Product Number
None (Operator Only)	Black	CR104PBG00B2
None (Operator Only)	Red	CR104PBG00R2
None (Operator Only)	Green	CR104PBG00G2
None (Operator Only)	1 Each: Red, Green, Yellow, Black	CR104PBG00U2 ¹
None (Operator Only)	1 Each: Brown, Blue, Orange, White	CR104PBG00V2 ¹
None (Operator Only)	Other	CR104PBG00*2 ²
1NO-1NC	Black	CR104PBG91B2
1NO-1NC	Red	CR104PBG91R2
1NO-1NC	Green	CR104PBG91G2
1NO-1NC	1 Each: Red, Green, Yellow, Black	CR104PBG91U2 ¹
1NO-1NC	1 Each: Brown, Blue, Orange, White	CR104PBG91V2 ¹
1NO-1NC	Other	CR104PBG91*2 ²
2NO-2NC	Black	CR104PBG92B2
2NO-2NC	Red	CR104PBG92R2
2NO-2NC	Green	CR104PBG92G2
2NO-2NC	1 Each: Red, Green, Yellow, Black	CR104PBG92U2 ¹
2NO-2NC	1 Each: Brown, Blue, Orange, White	CR104PBG92V2 ¹
2NO-2NC	Other	CR104PBG92*2 ²
1NO	Black	CR104PBG10B2
1NO	Red	CR104PBG10R2
1NO	Green	CR104PBG10G2
1NO	1 Each: Red, Green, Yellow, Black	CR104PBG10U2 ¹
1NO	1 Each: Brown, Blue, Orange, White	CR104PBG10V2 ¹
1NO	Other	CR104PBG10*2 ²
1NC	Black	CR104PBG01B2
1NC	Red	CR104PBG01R2
1NC	Green	CR104PBG01G2
1NC	1 Each: Red, Green, Yellow, Black	CR104PBG01U2 ¹
1NC	1 Each: Brown, Blue, Orange, White	CR104PBG01V2 ¹
1NC	Other	CR104PBG01*2 ²



Extended Button

Recessed Button - Momentary Operator

Contact Configuration	Color	Product Number
None (Operator Only)	Black	CR104PBG00B3
None (Operator Only)	Red	CR104PBG00R3
None (Operator Only)	Green	CR104PBG00G3
None (Operator Only)	1 Each: Red, Green, Yellow, Black	CR104PBG00U3 ¹
None (Operator Only)	1 Each: Brown, Blue, Orange, White	CR104PBG00V3 ¹
None (Operator Only)	Other	CR104PBG00*3 ²
1NO-1NC	Black	CR104PBG91B3
1NO-1NC	Red	CR104PBG91R3
1NO-1NC	Green	CR104PBG91G3
1NO-1NC	1 Each: Red, Green, Yellow, Black	CR104PBG91U3 ¹
1NO-1NC	1 Each: Brown, Blue, Orange, White	CR104PBG91V3 ¹
1NO-1NC	Other	CR104PBG91*3 ²
2NO-2NC	Black	CR104PBG92B3
2NO-2NC	Red	CR104PBG92R3
2NO-2NC	Green	CR104PBG92G3
2NO-2NC	1 Each: Red, Green, Yellow, Black	CR104PBG92U3 ¹
2NO-2NC	1 Each: Brown, Blue, Orange, White	CR104PBG92V3 ¹
2NO-2NC	Other	CR104PBG92*3 ²
1NO	Black	CR104PBG10B3
1NO	Red	CR104PBG10R3
1NO	Green	CR104PBG10G3
1NO	1 Each: Red, Green, Yellow, Black	CR104PBG10U3 ¹
1NO	1 Each: Brown, Blue, Orange, White	CR104PBG10V3 ¹
1NO	Other	CR104PBG10*3 ²
1NC	Black	CR104PBG01B3
1NC	Red	CR104PBG01R3
1NC	Green	CR104PBG01G3
1NC	1 Each: Red, Green, Yellow, Black	CR104PBG01U3 ¹
1NC	1 Each: Brown, Blue, Orange, White	CR104PBG01V3 ¹
1NC	Other	CR104PBG01*3 ²



Recessed Button

¹Supplied with 4 caps: Unassembled.

²To order assembled units with a different color, substitute the letter below in place of the * in product number and add required adder to the list price.

Cap Colors Available*

Color	Insert in place of asterisk (*)
Yellow	E
Blue	L
Orange	M
Brown	N
White	W
No Cap	A

