

# Illuminated Push Buttons

Type		Contacts		Lens Color		Ring		Lamp		Voltage	
C	R	1	0	4	P	B					

L = Full voltage  
R = Resistor  
T = Transformer

00 = None  
10 = 1NO  
01 = 1NC  
11 = 1NO/1NC  
92 = 2NO/2NC

F = Flashing  
L = LED  
N = Neon  
S = Standard

2 = 120V  
3 = 240V  
4 = 480V  
5 = 600V  
6 = 6V  
7 = 12V  
8 = 24V

**Other forms available:**

- Push-on, push-off
- 2-position push-pull mushroom-head
- 3-position push-pull mushroom-head
- Dual input (120v)

**Available Combinations**

Power Supply	Lamp	Lens Color Code (Digit 4)	Voltage						
			6	12	24	120	240	480	600
Full Voltage	Incandescent	All	■	■	■	■			
	LED	E,G,M,R	■	■	■	■			
	Neon	R,W,C				■			
	Flashing	All	■						
	Resistor	All				■	■		
Transformer	Incandescent	All				■	■	■	■
	LED	E,G,M,R				■	■	■	■
	Flashing	All				■	■	■	■

**Availability**

	Standard	Mushroom-head
1 = Extended	■	
3 = With guard	■	
5 = 1 3/8" (35mm)		■

**Availability**

	Standard	Mushroom-head
A = No lens/cap	■	
C = Clear	■	■
E = Yellow	■	■
G = Green	■	■
L = Blue	■	■
M = Amber	■	■
R = Red	■	■
W = White	■	■

**Tip for Quick Service:** For small quantity orders of illuminated operators in colors other than red or green, order operator with red/green lens and order other color lenses separately.