

Definite Purpose Controls Full Voltage Contactors

CR353
Standard
Three Phase
4-pole
25A-40A

For configurations not found below see page 4-9 for Factory Modified Forms.



CR353A Contactor

CR353 Standard (4-pole)

Inductive Amps	Resistive Amps	Locked Rotor Amps, 50/60 Hz @ 240V	Locked Rotor Amps, 50/60 Hz @ 480V	Locked Rotor Amps, 50/60 Hz @ 600V	No. of Poles	Product Number	List Price GO-10DP
25	35	150	125	100	4	CR353AB4A*1	\$71.00
30	40	180	150	120	4	CR353AC4A*1	\$77.00
40	50	240	200	160	4	CR353AD4B*1	\$95.00

(Replace * in product number with appropriate coil digit.)

Coil Selection

CR353A Coil Selection

AC Coils

Coil Voltage		Product No. Digit
60 Hz	50 Hz	
24	24	H
110-120	110-120	A
208-240	208-240	B
277	—	F
415-480	415-480	C
575-600	550	D

DC Coils

Voltage DC	Product No. Digit	List Price Adder GO-10DP
12	P	\$36.00
24-48	R	\$36.00
125	S	\$36.00



Definite Purpose Controls Full Voltage Contactors

CR353

Standard

Three Phase

4-pole

Factory Modified Forms

25A-40A

Factory Installed Modifications

CR353 Definite Purpose Contactors, 25A-40A, 4-pole

Select contactor from the main table and complete the product number by inserting the digits corresponding to required and optional specifications from the tables below. Note: minimum order quantities apply to all factory modified forms. Contact GE Consumer & Industrial sales engineer for details.

Full Load Amps	Resistive Amps Per Pole	Locked Rotor Amps, Three Phase, 50/60 Hz				Poles	Product Number (Complete by adding digits from tables below ¹)										List Price GO-10DP					
		240V	480V	600V	Required Digits																	
					1		2	3	4	5	6	7	8	9	10	11		12	13			
25	35	150	125	100	4	C	R	3	5	3	A	B	4									\$71.00
30	40	180	150	120	4	C	R	3	5	3	A	C	4									\$77.00
40	50	240	200	160	4	C	R	3	5	3	A	D	4									\$89.00

¹If no options are required, product number is complete after 10 digits.

Digit 9 Line and Load Terminals

Product No. Digit 9	Terminal Type	List Price Adder, GO-10DP	
		25-30A	40A
A	Screw w/ Quick Connect	\$0.00	\$6.00
B	Box Lug w/ Quick Connect	\$6.00	\$6.00
C	Screw	\$5.00	\$5.00
D	Lug	\$6.00	\$6.00

Digit 10 Coil Selection

AC Coils

Coil Voltage		Product No. Digit 10
60 Hz	50 Hz	
24	24	H
110-120	110-120	A
208-240	208-240	B
277	—	F
415-480	415-480	C
575-600	550	D

DC Coils

Coil Voltage	Product No. Digit 10	List Price Adder GO-10DP
12	P	\$36.00
24-48	R	\$36.00
110-125	S	\$36.00

Digit 11 Terminal Markings

Product No. Digit 11	Terminal Markings	List Price Adder GO-10DP
0	No terminal markings ²	\$1.00
1	Line (L) at top, Load (T) at bottom (Standard)	\$0.00
2	Load (T) at top, Line (L) at bottom (Inverted)	\$1.00

Digit 12 Auxiliary Contacts

Product No. Digit 12	Auxiliary Contacts	List Price Adder GO-10DP
A	None (standard) ²	\$0.00
B	10FLA, 250Vac SPDT on left side	\$16.00
C	10FLA, 250Vac, SPDT left & right	\$32.00

Digit 13 Nameplate Markings

For special nameplate markings, contact factory.

Product No. Digit 13	Specials	List Price Adder GO-10DP
Blank	None (standard)	\$0.00

²If this will be the final digit(s) in your selection, omit from product number.

