

## Definite Purpose Magnetic Contactors - Cross Reference

Poles	Amps	Volts	Arrow Hart	Cutler Hammer	Fasco	Fasco New	Furnas	Furnas Centurion	GE 353 Series	GE 453 Series	Rotom
1	25	24	C251U10	C25ANB125T	1S25A	-	-	-	CR353CB1AH1	-	HC-13024
		120	C251U20	C25ANB125A	1S25B	-	-	-	CR353CB1AA1	-	HC-130120
		208/240	C251U30	C25ANB125B	1S25C	-	-	-	CR353CB1AB1	-	HC130240
1	30	24	C301U10	C25ANB130T	1S30A	C1S30A	-	-	CR353CC1AH1	-	HC-13024
		120	C301U20	C25ANB130A	1S30B	C1S30B	-	-	CR353CC1AA1	-	HC-130120
		208/240	C301U30	C25ANB130B	1S30C	C1S30C	-	-	CR353CC1AB1	-	HC-130240
1	40	24	-	C25ANB140T	-	C1S40A	-	-	CR353CD1AH1	-	HC-24024
		120	-	C25ANB140A	-	C1S40B	-	-	CR353CD1AA1	-	HC-240120
		208/240	-	C25ANB140B	-	C1S40C	-	-	CR353CD1AB1	-	HC-240240
1.5	25	24	C251NU10	C25CNB125T	-	-	45DD10AJLL2	45DG10AJD8A	CE353CB3AH1	CR453CB3HAA	HC-23024
		120	C251NU20	C25CNB125A	-	-	45DD10AFLL2	45DG10AFD8A	CR353CB3AA1	CR453CB3AAA	HC-230120
		208/240	C251NU30	C25CNB125B	-	-	45DD10AGLL2	45DG10AGD8A	CR353CB3AB1	CR453CB3BAA	HC-230240
1.5	30	24	C301NU10	C25CNB130T	-	-	45ED10AJLL2	45EG10AJA	CR353CC3AH1	CR453CC3HAA	HC-23024
		120	C301NU20	C25CNB130A	-	-	45ED10AFLL2	45EG10AFA	CR353CC3AA1	CR453CC3AAA	HC-230120
		208/240	C301NU30	C25CNB130B	-	-	45ED10AGLL2	45EG10AGA	CR353CC3AB1	CR453CC3BAA	HC-230240
1.5	40	24	-	C25CNB140T	-	-	45GD10AJ	45GG10AJA	CR353CD3AH1	CR453CD3HAA	HC-24024
		120	-	C25CNB140A	-	-	45GD10AF	45GG10AFA	CR353CD3AA1	CR453CD3AAA	HC-240120
		208/240	-	C25CNB140B	-	-	45GD10AG	45GG10AGA	CR353CD3AB1	CR453CD3BAA	HC-240240
2	20	24	C202U10	C25BNB220T	2S20A	-	45CA20AJ	45CG20AJ	CR353CA2AH1	CR453CA2HAA	H2-23024
		120	C202U20	C25BNB220A	2S20B	-	45CA20AF	45CG20AF	CR353CA2AA1	CR453CA2AAA	HC-230120
		208/240	C202U30	C25BNB220B	2S20C	-	45CA20AG	45CG20AG	CR353CA2AB1	CR453CA2BAA	HC-230240
2	25	24	C252U10	C25BNB225T	2S25A	-	45DA20AJ	45DG20AJ	CR353CB2AH1	CR453CB2HAA	H2-23024
		120	C252U20	C25BNB225A	2S25B	-	45DA20AF	45DG20AF	CR353CB2AA1	CR453CB2AAA	HC-230120
		208/240	C252U30	C25BNB225B	2S25C	-	45DA20AG	45DG20AG	CR353CB2AB1	CR453CB2BAA	HC-230240
2	25	24	ACC220U10	C25DND225T	-	-	41NB20AJM	42AF15AJ	CR353AB2AH1	-	HC-23024
		120	ACC220U20	C25DND225A	-	-	41NB20AFM	42AF15AF	CR353AB2AA1	-	HC-230120
		208/240	ACC220U30	C25DND225B	-	-	41NB20AGM	42AF15AG	CR353AB2AB1	-	HC-230240
2	30	24	C302U10	C25BNB230T	2S30A	C2S30A	45EA20AJ	45EG20AJ	CR353CC2AH1	CR453CC2HAA	H2-23024
		120	C302U20	C25BNB230A	2S30B	C2S30B	45EA20AF	45EG20AF	CR353CC2AA1	CR453CC2AAA	HC-230120
		208/240	C302U30	C25BNB230B	2S30C	C2S30C	45EA20AG	45EG20AG	CR353CC2AB1	CR453CC2BAA	HC-230240
2	30	24	ACC320U10	C25DND230T	-	-	42BE15AJ106	42BF15AJ	CR353AC2AH1	-	HC-23024
		120	ACC320U20	C25DND230A	-	-	42BE15AF106	42BF15AF	CR353AC2AA1	-	HC-230120
		208/240	ACC320U30	C25DND230B	-	-	42BE15AG106	42BF15AG	CR353AC2AB1	-	HC-230240
2	40	24	C402U10	C25BNB240T	2M40A	C2S40A	45GA20AJ	45GG20AJ	CR353CE2BH1	CR453CE2HBB	HC-24024
		120	C402U20	C25BNB240A	2M40B	C2S40B	45GA20AF	45GG20AF	CR353CE2BA1	CR453CE2ABB	HC-240120
		208/240	C402U30	C25BNB240B	2M40C	C2S40C	45GA20AG	45GG20AG	CR353CE2BB1	CR453CE2BBB	HC-240240
2	40	24	ACC420U10	C25DNF240T	-	-	42CE15AJ106	42CF15AJ	CR353AD2AH1	-	HC-24024
		120	ACC420U20	C25DNF240A	-	-	42CE15AF106	42CF15AF	CR353AD2AA1	-	HC-240120
		208/240	ACC420U30	C25DNF240B	-	-	42CE15AG106	42CF15AG	CR353AD2AB1	-	HC-240240
2	50	24	ACC520U10	C25FNF250T	-	-	42DE15AJ106	42DF15AJ	CR353FE2BH1	-	HC-35024
		120	ACC520U20	C25FNF250A	-	-	42DE15AF106	42DF15AF	CR353FE2BA1	-	HC-350120
		208/240	ACC520U30	C25FNF250B	-	-	42DE15AG106	42DF15AG	CR353FE2BB1	-	HC-350240
2	60	24	ACC620U10	C25FNF260T	-	-	42EE15AJ106	42EF15AJ	CR353FF2BH1	-	HC-36024
		120	ACC620U20	C25FNF260A	-	-	42EE15AF106	42EF15AF	CR353FF2BA1	-	HC-360120
		208/240	ACC620U30	C25FNF260B	-	-	42EE15AG106	42EF15AG	CR353FF2BB1	-	HC-360240
3	25	24	ACC230U10	C25DND325T	3M25A	-	41NB30AJM	42AF35AJ	CR353AB3AH1	CR453AB3HAA	HC-33024
		120	ACC230U20	C25DND325A	3M25B	-	41NB30AFM	42AF35AF	CR353AB3AA1	CR453AB3AAA	HC-330120
		208/240	ACC230U30	C25DND325B	3M25C	-	41NB30AGM	42AF35AG	CR353AB3AB1	CR453AB3BAA	HC-330240
3	30	24	ACC330U10	C25DND330T	3M30A	C3M30A	42BE35AJ106	42BF35AJ	CR353AC3AH1	CR453AC3HAA	HC-33024
		120	ACC330U20	C25DND330A	3M30B	C3M30B	42BE35AF106	42BF35AF	CR353AC3AA1	CR453AC3AAA	HC-330120
		208/240	ACC330U30	C25DND330B	3M30C	C3M30C	42BE35AG106	42BF35AG	CR353AC3AB1	CR453AC3BAA	HC-330240
3	40	24	ACC430U10	C25DNF340T	3M40A	C3M40A	42CE35AJ106	42CF35AJ	CR353AD3BH1	CR453AD3HBB	HC-34024
		120	ACC430U20	C25DNF340A	3M40B	C3M40B	42CE35AF106	42CF35AF	CR353AD3BA1	CR453AD3ABB	HC-340120
		208/240	ACC430U30	C25DNF340B	3M40C	C3M40C	42CE35AG106	42CF35AG	CR353AD3BB1	CR453AD3BBB	HC-340240
3	50	24	ACC530U10	C25FNF350T	3L50A	C3L50A	42DE35AJ106	42DF35AJ	CR353FE3BH1	-	HC-35024
		120	ACC530U20	C25FNF350A	3L50B	C3L50B	42DE35AF106	42DF35AF	CR353FE3BA1	-	HC-350120
		208/240	ACC530U30	C25FNF350B	3L50C	C3L50C	42DE35AG106	42DF35AG	CR353FE3BB1	-	HC-350240
3	60	24	ACC630U10	C25FNF360T	3L60A	C3L60A	42EE35AJ106	42EF35AJ	CR353FF3BH1	-	HC-36024
		120	ACC630U20	C25FNF360A	3L60B	C3L60B	42EE35AF106	42EF35AF	CR353FF3BA1	-	HC-360120
		208/240	ACC630U30	C25FNF360B	3L60C	C3L60C	42EE35AG106	42EF35AG	CR353FF3BB1	-	HC-360240
4	25	24	-	C25END425T	-	-	42AF25AJ	42AF25AJ	CR353AB4AH1	-	HC-43024
		120	-	C25END425A	-	-	42AF25AF	42AF25AF	CR353AB4AA1	-	HC-430120
		208/240	-	C25END425B	-	-	42AF25AG	42AF25AG	CR353AB4AB1	-	HC-430240
4	30	24	ACC34U10	C25END430T	-	C4L30A	42BE25AJ106	42BF25AJ	CR353AC4AH1	-	HC-43024
		120	ACC34U20	C25END430A	-	C4L30B	42BE25AF106	42BF25AF	CR353AC4AA1	-	HC-430120
		208/240	ACC34U30	C25END430B	-	C4L30C	42BE25AG106	42BF25AG	CR353AC4AB1	-	HC-430240
4	40	24	ACC440U10	C25ENF440T	-	C4L40A	42CE25AJ106	42CF25AJ	CR353AD4BH1	-	HC-44024
		120	ACC440U20	C25ENF440A	-	C4L40B	42CE25AF106	42CF25AF	CR353AD4BA1	-	HC-440120
		208/240	ACC440U30	C25ENF440B	-	C4L40C	42CE25AG106	42CF25AG	CR353AD4BB1	-	HC-440240

### Contactors Nomenclature • HC - 1 30 24

HC = Product Code • 1 = Poles (1, 2, 3 or 4) • 30 = Full Load Amps. (30A, 40A...) • 24 = Coil Voltage (24, 120 or 240)