

Definite Purpose Controls Full Voltage Contactors

Section 4

CR453A, CR353

Standard

Coils and Renewal Parts

25A-150A

AC Replacement Coil

Contactor Prefix	Inductive Amps	Coil Letter Code	Coil Voltage @ 60 Hz	Coil Voltage @ 50 Hz	Product Number	List Price GO-11G
CR453A, CR454A, CR455A	25-40	A	110-120	110-120	55-537283A	\$24.00
CR453A, CR454A, CR455A	25-40	B	208-240	208-240	55-537283B	\$24.00
CR453A, CR454A, CR455A	25-40	C	440-480	380-415	55-537283C	\$24.00
CR453A, CR454A, CR455A	25-40	D	550-600	550-600	55-537283D	\$24.00
CR453A, CR454A, CR455A	25-40	E	12	12	55-537283E	\$24.00
CR453A, CR454A, CR455A	25-40	F	277	—	55-537283F	\$24.00
CR453A, CR454A, CR455A	25-40	H	24	24	55-537283H	\$24.00
CR353A, CR354A, CR355A	25-40	A	110-120	110-120	55-B31A	\$24.00
CR353A, CR354A, CR355A	25-40	B	208-240	208-240	55-B31B	\$24.00
CR353A, CR354A, CR355A	25-40	C	415-480	415-480	55-B31C	\$24.00
CR353A, CR354A, CR355A	25-40	D	575-600	550	55-B31D	\$24.00
CR353A, CR354A, CR355A	25-40	F	277	—	55-B31F	\$24.00
CR353A, CR354A, CR355A	25-40	H (4 pole)	24	24	55-B31H	\$24.00
CR353A, CR354A, CR355A	25-40	H (2-3 pole)	24	24	55-B34H	\$24.00
CR353FE, CR353F, CR354FE, CR354F	50-60	A	110-120	110-120	55-B38A	\$30.00
CR353FE, CR353F, CR354FE, CR354F	50-60	B	208-240	208-240	55-B38B	\$30.00
CR353FE, CR353F, CR354FE, CR354F	50-60	C	440-480	380-415	55-B38C	\$30.00
CR353FE, CR353F, CR354FE, CR354F	50-60	D	575-600	550	55-B38D	\$30.00
CR353FE, CR353F, CR354FE, CR354F	50-60	F	277	—	55-B38F	\$30.00
CR353FE, CR353F, CR354FE, CR354F	50-60	H	24	24	55-B38H	\$30.00
CR355EE, CR355F	50-60	A	110-120	110-120	55-B21A	\$54.00
CR355EE, CR355F	50-60	B	208-240	208-240	55-B21B	\$54.00
CR355EE, CR355F	50-60	C	415-480	415-480	55-B21C	\$54.00
CR355EE, CR355F	50-60	D	575-600	550	55-B21D	\$54.00
CR355EE, CR355F	50-60	F	277	—	55-B21F	\$54.00
CR355EE, CR355F	50-60	H	24	24	55-B21H	\$54.00
CR353EG, CR353H, CR355EG, CR355H	75-90	A	110-120	110-120	55-B22A	\$60.00
CR353EG, CR353H, CR355EG, CR355H	75-90	B	208-240	208-240	55-B22B	\$60.00
CR353EG, CR353H, CR355EG, CR355H	75-90	C	440-480	380-415	55-B22C	\$60.00
CR353EG, CR353H, CR355EG, CR355H	75-90	D	575-600	550	55-B22D	\$60.00
CR353EG, CR353H, CR355EG, CR355H	75-90	F	277	—	55-B22F	\$60.00
CR353EG, CR353H, CR355EG, CR355H	75-90	H	24	24	55-B22H	\$60.00
CR353GJ	120	A	115-120	110	55-501336G002	\$148.00
CR353GJ	120	B	230-240	220	55-501336G003	\$148.00
CR353GJ	120	C	460-480	440	55-501336G004	\$148.00
CR353GJ	120	D	575-600	550	55-501336G005	\$148.00
CR353GK	150	A	115-120	110	55-501563G002	\$202.00
CR353GK	150	B	230-240	220	55-501563G003	\$202.00
CR353GK	150	C	460-480	440	55-501563G004	\$202.00
CR353GK	150	D	575-600	550	55-501563G005	\$202.00

