

Medium Voltage Equipment

Motor Control – Limitamp™

Frequently Requested Limitamp Renewal Parts

CR194 and CR7160

Limitamp Renewal Parts

Limitamp Type Part	Description	CR194	CR7160	Product Number
Arc Chute Assembly	Load Break Switch		•	204B4051BTG1
Blade Assembly	Load Break Switch		•	204B4051BRG1
		N/A		9F60DJD025
		N/A		9F60DJD030
		N/A		9F60DJD040
		N/A		9F60DJD050
	9F60 Series	N/A		9F60DJD065
		N/A		9F60DJD080
		N/A		9F60DJD100
		N/A		9F60DJD125
		N/A		9F60DJD150
		N/A		9F60DJD200
		•	•	9F62HCB025
		•	•	9F62HCB030
		•	•	9F62HCB040
		•	•	9F62HCB050
E Rated Fuses	9F62 G.P. Series	•	•	9F62HCB065
	Equivalent Cont.	•	•	9F62DCB080
	Current Rating	•	•	9F62DCB100
		•	•	9F62DCB125
		•	•	9F62DCB150
		•	•	9F62DCB175
		•	•	9F62DCB200
		•	•	9F62HCB025
		•	•	9F62HCB030
		•	•	9F62HCB040
		•	•	9F62HCB050
	9F62 G.P. Series	•	•	9F62HCB065
	Equivalent XFMR Protection	•	•	9F62DCB080
		•	•	9F62DCB125
		•	•	9F62DCB150
		•	•	9F62DCB175
		•	•	218A4291P2RB
	Air - Clip (5kV, 70A)	•	•	218A4291P3RB
	Air - Clip (5kV, 100A)	•	•	218A4291P4RB
	Air - Clip (5kV, 130A)	•	•	218A4291P6RB
	Air - Clip (5kV, 170A)	•	•	218A4291P9RB
	Air - Clip (5kV, 200A)	•	•	218A4291P12RB
	Air - Clip (5kV, 230A)	•	•	218A4291P18RB
	Air - Clip (5kV, 390A)	•	•	218A4291P24RB
	Air - Bolted (5kV, 70A)	•	•	218A4293P2RB
	Air - Bolted (5kV, 100A)	•	•	218A4293P3RB
	Air - Bolted (5kV, 130A)	•	•	218A4293P4RB
	Air - Bolted (5kV, 170A)	•	•	218A4293P6RB
	Air - Bolted (5kV, 200A)	•	•	218A4293P9RB
	Air - Bolted (5kV, 230A)	•	•	218A4293P12RB
	Air - Bolted (5kV, 390A)	•	•	218A4293P18RB
	Air - Bolted (5kV, 450A)	•	•	218A4293P24RB
	Vac. - Bolted (5kV, 70A)	•		55A212942P2RB
	Vac. - Bolted (5kV, 100A)	•		55A212942P3RB
	Vac. - Bolted (5kV, 130A)	•		55A212942P4RB
	Vac. - Bolted (5kV, 170A)	•		55A212942P6RB
	Vac. - Bolted (5kV, 200A)	•		55A212942P9RB
	Vac. - Bolted (5kV, 230A)	•		55A212942P12RB
	Vac. - Bolted (5kV, 390A)	•		55A212942P18RB
	Vac. - Bolted (5kV, 450A)	•		55A212942P24RB
R Rated Fuses	Vac. - Bolted - 800A (5kV, 425A)	•		55A213937P425B
	Vac. - Bolted - 800A (5kV, 550A)	•		55A213937P550B
	Vac. - Bolted - 800A (5kV, 630A)	•		55A213937P630B
	Vac. - Bolted - 800A (5kV, 800A)	•		55A213937P800B
	Air - Bolted (7.2kV, 70A)		•	218A4298P070
	Air - Bolted (7.2kV, 100A)		•	218A4298P100
	Air - Bolted (7.2kV, 180A)		•	218A4298P180
	Air - Bolted (7.2kV, 360A)		•	218A4298P360
	Vac. - Bolted (7.2kV, 70A)	•		55A212943P70
	Vac. - Bolted (7.2kV, 100A)	•		55A212943P100
	Vac. - Bolted (7.2kV, 180A)	•		55A212943P180
	Vac. - Bolted (7.2kV, 360A)	•		55A212943P360

