

Panelboards

A-Series® Panelboards

Accessories

Field Installed Kits/Replacement Parts

Order By Product Number from Factory

Enclosures¹

Panel Size	Box Product Number	Box Size Inches ²	List Price, ³ GO-134B	Front Product Number ⁴	List Price, ³ GO-134B
0-25.5	AB25B	25.5	\$166.00	AF25F,S	\$170.00
28.5-31.5	AB31B	31.5	\$170.00	AF31F,S	\$174.00
34.5-37.5	AB37B	37.5	\$182.00	AF37F,S	\$191.00
40.5-43.5	AB43B	43.5	\$204.00	AF43F,S	\$218.00
46.5-49.5	AB49B	49.5	\$233.00	AF49F,S	\$257.00
52.5-55.5	AB55B	55.5	\$261.00	AF55F,S	\$299.00
57.5-64.5	AB64B	64.5	\$286.00	AF64F,S	\$326.00
67.5-76.5	AB76B	76.5	\$324.00	AF76F,S	\$367.00

¹"B" suffix provides blank end walls. Order "K" suffix for endwalls with knockouts.

²Standard boxes are 20" wide by 5.81 inches deep.

³Use when ordering items separately for replacement. Do not deduct from panel list price to obtain interior only pricing.

⁴Flush fronts are 1 1/2" larger than box. Surface fronts are 1/4" larger.

Box Options

Description	Product Number Suffix ⁵	List Price, GO-101
Painted Box	P	\$200.00
30" wide ⁶	W	\$250.00
NEMA 3R/12/4S/4X	3	\$950.00
NEMA 4X (Stainless Steel)	4S	\$4950.00

⁵Add to base box product number.

⁶Includes field installable gutter barrier.

Front Options

Description	Product Number Suffix ⁷	List Price, GO-101
Screw cover	C	\$61.00
Front hinged to box	D	\$110.00
Optional Locks:		
Yale 5116 w/Rosette	Y	\$300.00
Corbin 15767	L	\$146.00
GE 75 Key Lock	E	\$80.00
Corbin 60 Key Lock	J	\$80.00
Door within a door ⁸	P	\$238.00
Stainless steel ⁹	S	\$1467.00
30" wide	W	\$82.00
Nameplate	N	\$27.00
Screw on nameplate	U	\$74.00
Metal directory	M	\$50.00

⁷Add to base front product number.

⁸Consists of two lockable doors—one over panel interior and one over box wiring gutters. Yale locks not available.

⁹Flush only. Available with C and N options.

THQB/THHQB/THQL/THHQL/TEY Filler Plates

Product Number	List Price GO-137A
TQLFP1	\$2.50

TQD/THQD/TED4/SE/FB Filler Plates

Product Number	List Price GO-101
TEDFP1	\$1.00

Breaker Mounting¹⁰ Hardware Kits

Product Number	List Price GO-134B
ASPTED3P (Breaker type TED/THED4/SE)	\$83.50
ASPTQD3P (Breaker type TQD/THQD)	\$83.50
ASPFB12P (Breaker type FB)	\$20.00¹¹

¹⁰Use to mount breaker in existing space.

¹¹GO-101.

Stainless Steel Enclosures for GE Lighting Panels

Dimensions (inches)			Product Number ¹²		List Price Each GO-134B
H	W	D	UL Standard	CSA Labeled	
25.5	20	6	AB254S	AB254AS	\$1245.00
25.5	30	8	AB254DWS	AB254DWAS	\$1305.00
31.5	20	6	AB314S	AB314AS	\$1475.00
31.5	30	8	AB314DWS	AB314DWAS	\$1550.00
37.5	20	6	AB374S	AB374AS	\$1730.00
37.5	30	8	AB374DWS	AB374DWAS	\$1815.00
43.5	20	6	AB434S	AB434AS	\$1955.00
43.5	30	8	AB434DWS	AB434DWAS	\$2055.00
49.5	20	6	AB494S	AB494AS	\$2185.00
49.5	30	8	AB494DWS	AB494DWAS	\$2295.00
55.5	20	6	AB554S	AB554AS	\$2245.00
55.5	30	8	AB554DWS	AB554DWAS	\$2570.00
64.5	20	6	AB644S	AB644AS	\$2785.00
64.5	30	8	AB644DWS	AB644DWAS	\$2925.00
76.5	20	6	AB764S	AB764AS	\$3265.00
76.5	30	8	AB764DWS	AB764DWAS	\$3430.00

¹²DW in product number indicates enclosure is 30" wide and 8" deep.



Publications and Reference: See Section 22 for a complete list of additional product-related publications