

Panelboards

A-Series® Panelboards

Pro-Stock, Unassembled Lighting Panels

6 Select Main Lug Kit and Accessories

Select lug kit(s) for main lug and/or feed-thru applications, if required. (All lugs are suitable for interiors with either copper or aluminum bus.) Also select any accessories required.



Main Lug Kits

Lug Type	Amp Rating	Standard			Oversized			200% Neutral	
		Product Number	List Price GO-101P	Wire Range	Product Number	List Price GO-101P	Wire Range	Product Number	List Price GO-101P
Pressure	225	MLA1	\$30.00	6-350 MCM	MLA2	\$52.00	1-600 MCM or (2) 1/0-250 MCM	NKA	\$25.00
	400	MLA41	\$60.00	2-600 MCM or (2) 1/0-250 MCM	MLA62	\$100.00	3/0-800 MCM	NKA4 ²	\$50.00
	600	MLA61	\$90.00	(2) 2/0-500 MCM	MLA62	\$100.00	3/0-800 MCM	-	-
Copper	225	MLR1	\$65.00	4-350 MCM	MLR2	\$105.00	1-600 MCM	NKR	\$43.00
	400	MLR41	\$120.00	1-600 MCM	MLR61	\$175.00	(2) 2/0-500 MCM	NKR4	\$80.00
	600	MLR61	\$175.00	(2) 2/0-500 MCM	-	-	-	-	-
Compression	225	MLT1	\$65.00	2/0-300 MCM	MLT2	\$105.00	4/0-500 MCM	NKT	\$43.00
	400	MLT42	\$120.00	250-600 MCM	MLT41	\$120.00	500-750 MCM ¹	NKT4	\$80.00
Dual	225	MLA2	\$52.00	1-600 MCM or (2) 1/0-250 MCM	-	-	-	-	-
Main	400	MLA61	\$90.00	(2) 2/0-500 MCM	-	-	-	-	-

¹500 MCM Cu, 750 MCM Al.

²For 200% neutral feed-thru, order NKA4FT, List Price \$85.00 (GO-101P). Wire range (2) 2/0 - 600 MCM or (4) 4-250 MCM.

Accessories

Service Entrance ³			ProCare Kit ⁴		
Amp Rating	Product Number	List Price, GO-101P	Description	Product Number	List Price, GO-101P
225A	BNDKT	\$15.00	ProCare Kit for Pro-Stock panelboard installation and maintenance	PROCARE	\$100.00
400A	BNDKT6	\$30.00			
600A	BNDKT6	\$30.00			

³Service entrance kit includes a bonding strap with hardware and a service entrance label.

⁴ProCare Kit includes: (5) filler plate hardware kits, (9) bus stud nuts, (5) MLA1 filler plates, (2) 225A phase barriers, (2) feed-thru barriers, (1) 400/600A phase barrier, (50) directory cards/rating books, (50) circuit number strips (1-48), (50) circuit number strips (43-84), (5) standard locks and keys, (50) deadfront screws, (10) AQ/AE front hardware kits, (10) AD front hardware kits, (50) service disconnect labels, (50) main labels.

7 Typical Bolt-On Branch Breakers

These tables show typical branch breakers, but do not include all branch breakers that can be used with Pro-Stock panelboards.

Branch circuit breakers for use with AQ panels (208/120 Vac 3-phase or 240 Vac single phase)

Amp Rating	10kAIC						22kAIC					
	1-pole		2-pole		3-pole		1-pole		2-pole		3-pole	
	Product Number	List Price GO-135B	Product Number	List Price GO-135B	Product Number	List Price GO-135B	Product Number	List Price GO-135B	Product Number	List Price GO-135B	Product Number	List Price GO-135B
15	THQB1115	\$19.75	THQB2115	\$43.50	THQB32015	\$139.00	THHQB1115	\$35.00	THHQB2115	\$82.50	THHQB32015	\$212.00
20	THQB1120	\$19.75	THQB2120	\$43.50	THQB32020	\$139.00	THHQB1120	\$35.00	THHQB2120	\$82.50	THHQB32020	\$212.00
25	THQB1125	\$19.75	THQB2125	\$43.50	THQB32025	\$139.00	THHQB1125	\$39.00	THHQB2125	\$82.50	THHQB32025	\$212.00
30	THQB1130	\$19.75	THQB2130	\$43.50	THQB32030	\$139.00	THHQB1130	\$39.00	THHQB2130	\$82.50	THHQB32030	\$212.00
35	THQB1135	\$19.75	THQB2135	\$43.50	THQB32035	\$139.00	THHQB1135	\$39.00	THHQB2135	\$82.50	THHQB32035	\$212.00
40	THQB1140	\$19.75	THQB2140	\$43.50	THQB32040	\$139.00	THHQB1140	\$39.00	THHQB2140	\$82.50	THHQB32040	\$212.00
45	THQB1145	\$19.75	THQB2145	\$43.50	THQB32045	\$139.00	THHQB1145	\$39.00	THHQB2145	\$82.50	THHQB32045	\$212.00
50	THQB1150	\$19.75	THQB2150	\$43.50	THQB32050	\$139.00	THHQB1150	\$39.00	THHQB2150	\$82.50	THHQB32050	\$212.00
60	THQB1160	\$19.75	THQB2160	\$43.50	THQB32060	\$139.00	THHQB1160	\$39.00	THHQB2160	\$82.50	THHQB32060	\$212.00
70	THQB1170	\$38.00	THQB2170	\$82.50	THQB32070	\$175.00	THHQB1170	\$51.00	THHQB2170	\$126.00	THHQB32070	\$263.00
80	-	-	THQB2180	\$113.00	THQB32080	\$199.00	-	-	THHQB2180	\$183.00	THHQB32080	\$307.00
90	-	-	THQB2190	\$113.00	THQB32090	\$199.00	-	-	THHQB2190	\$183.00	THHQB32090	\$307.00
100	-	-	THQB21100	\$113.00	THQB32100	\$199.00	-	-	THHQB21100	\$183.00	THHQB32100	\$307.00

Branch circuit breakers for use with AE panels (480/277 Vac 3-phase)

Amp Rating	14kAIC					
	1-pole		2-pole		3-pole	
	Product Number	List Price GO-135B	Product Number	List Price GO-135B	Product Number	List Price GO-135B
15	TEY115	\$72.00	TEY215	\$216.00	TEY315	\$316.00
20	TEY120	\$72.00	TEY220	\$216.00	TEY320	\$316.00
30	TEY130	\$72.00	TEY230	\$216.00	TEY330	\$316.00
40	TEY140	\$72.00	TEY240	\$216.00	TEY340	\$316.00
50	TEY150	\$72.00	TEY250	\$216.00	TEY350	\$316.00
60	TEY160	\$72.00	TEY260	\$216.00	TEY360	\$316.00
70	TEY170	\$142.00	TEY270	\$352.00	TEY370	\$424.00
80	TEY180	\$142.00	TEY280	\$352.00	TEY380	\$424.00
90	TEY190	\$142.00	TEY290	\$352.00	TEY390	\$424.00
100	TEY1100	\$142.00	TEY2100	\$352.00	TEY3100	\$424.00

