

Safety Switches Heavy Duty, Type TH

Spec-Setter™ Safety Switches

30-1200 Amperes

240, 480, 600 Volts AC

600 Volts DC

Section 4



TH3361RF

Three-pole, 480, 480Y/277¹ and 600 Volts AC-250 DC, Fusible

Ampere Rating	Enclosure Type	HP, 480 Vac, NEC Std, 3-ph	HP, 600 Vac, NEC Std, 3-ph	HP, 480 Vac, Time Delay, 3-ph	HP, 600 Vac, Time Delay, 3-ph	HP, 125 Vdc	HP, 250 Vdc	HP, 600 Vdc	Product Number
30A	NEMA Type 1	5	7 1/2	15	20	-	5	-	TH3361
60A	NEMA Type 1	15	15	30	50	-	10	-	TH3362
100A	NEMA Type 1	25	30	60	75	-	20	-	TH3363
200A	NEMA Type 1	50	60	125	150	-	40	-	TH3364
400A	NEMA Type 1	100	125	250	350	-	50	-	TH3365
600A	NEMA Type 1	150	200	400	500	-	50	-	TH3366
800A	NEMA Type 1	-	-	-	-	-	-	-	TC2367 ²
1200A	NEMA Type 1	-	-	-	-	-	-	-	TC2368 ²
30A	NEMA Type 3R	5	7 1/2	15	20	-	5	-	TH3361R
30A	NEMA Type 3R	5	7 1/2	15	20	-	5	-	TH3361RF ⁴
60A	NEMA Type 3R	15	15	30	50	-	10	-	TH3361RF ⁴
60A	NEMA Type 3R	15	15	30	50	-	10	-	TH3362R
60A	NEMA Type 3R	15	15	30	50	-	10	-	TH3362RF ⁴
100A	NEMA Type 3R	25	30	60	75	-	20	-	TH3363R
200A	NEMA Type 3R	50	60	125	150	-	40	-	TH3364R ⁶
400A	NEMA Type 3R	100	125	250	350	-	50	-	TH3365R
600A	NEMA Type 3R	150	200	400	500	-	50	-	TH3366R
800A	NEMA Type 3R	-	-	-	-	-	-	-	TC2367R ^{2,3}
1200A	NEMA Type 3R	-	-	-	-	-	-	-	TC2368R ^{2,3}
30A	NEMA Type 4/4X	5	7 1/2	15	20	-	5	-	TH3361SS ⁷
60A	NEMA Type 4/4X	15	15	30	50	-	10	-	TH3362SS ⁷
100A	NEMA Type 4/4X	25	30	60	75	-	20	-	TH3363SS ⁷
200A	NEMA Type 4/4X	50	60	125	150	-	40	-	TH3364SS ^{6,7}
400A	NEMA Type 4/4X	100	125	250	350	-	50	-	TH3365SS
600A	NEMA Type 4/4X	150	200	400	500	-	50	-	TH3366SS
30A	NEMA Type 5, 12	5	7 1/2	15	20	-	5	-	TH3361J
60A	NEMA Type 5, 12	15	15	30	50	-	10	-	TH3362J
100A	NEMA Type 5, 12	25	30	60	75	-	20	-	TH3363J
200A	NEMA Type 5, 12	50	60	125	150	-	40	-	TH3364J ⁶
400A	NEMA Type 5, 12	100	125	250	350	-	50	-	TH3365J
600A	NEMA Type 5, 12	150	200	400	500	-	50	-	TH3366J
30A	NEMA Type 3R, 5, 12	5	7 1/2	15	20	-	5	-	TH3361JR
60A	NEMA Type 3R, 5, 12	15	15	30	50	-	10	-	TH3362JR
100A	NEMA Type 3R, 5, 12	25	30	60	75	-	20	-	TH3363JR
200A	NEMA Type 3R, 5, 12	50	60	125	150	-	40	-	TH3364JR ⁶
400A	NEMA Type 3R, 5, 12	100	125	250	350	-	50	-	TH3365JR ⁸
600A	NEMA Type 3R, 5, 12	150	200	400	500	-	50	-	TH3366JR ⁸

Four-pole, 480 and 600 Volts AC, Fusible⁵

Ampere Rating	Enclosure Type	HP, 480 Vac, NEC Std, 2-ph	HP, 600 Vac, NEC Std, 2-ph	HP, 480 Vac, Time Delay, 2-ph	HP, 600 Vac, Time Delay, 2-ph	HP, 125 Vdc	HP, 250 Vdc	HP, 600 Vdc	Product Number
30A	NEMA Type 1, 3R, 5, 12	7 1/2	10	20	25	-	5	-	TH6661
60A	NEMA Type 1, 3R, 5, 12	15	20	40	50	-	10	-	TH6662
100A	NEMA Type 1, 3R, 5, 12	20	30	50	50	-	20	-	TH6663
200A	NEMA Type 1, 3R, 5, 12	50	50	-	-	-	40	-	TH6664

For Type 1 Enclosure: 200-600 amp devices available factory reversed for bottom feed. Add "B" suffix to product number (e.g., TH33365B). UL Listed.

For Type 3R Enclosure: 30-200 amp devices have removable closing cap. Order hubs for these devices separately on page 4-29. Larger amp devices require field cut openings and **customer-supplied** hub.

¹Order neutral kits from pages 4-24 and 4-26.

²Rated 600 Vac only. Accepts Class L fuses only. Type HD electrical performance does not apply.

³Not CSA Certified

⁴Farm switch with oversize Type 3R enclosure and vertical hinge. See enclosure dimensions on page 4-31.

⁵Use four poles of six-pole

⁶Rated to maximum 100,000 ampere interrupting capacity.

⁷Available with "-BA" suffix for ARRA compliance. Same list price and GO schedule. Contact GE Sales Office for other ARRA compliant safety switches.

⁸Not UL Listed.

