

Safety Switches Heavy Duty, Type TH

Spec-Setter™ Safety Switches

30-1200 Amperes

240, 480, 600 Volts AC

600 Volts DC

Section 4

Two-pole, 600 Volts DC, No Fuse

Ampere Rating	Enclosure Type	HP, 240 Vac, NEC Std, 1-ph	HP, 240 Vac, NEC Std, 3-ph	HP, 480 Vac, Time Delay, 3-ph	HP, 600 Vac, Time Delay, 3-ph	HP, 125 Vdc	HP, 250 Vdc	HP, 600 Vdc	Product Number
30A	NEMA Type 1	–	–	–	–	–	–	15	THN2261DC
60A	NEMA Type 1	–	–	–	–	–	–	25	THN2262DC
100A	NEMA Type 1	–	–	–	–	–	–	25	THN2263DC
30A	NEMA Type 3R	–	–	–	–	–	–	15	THN2261RDC
60A	NEMA Type 3R	–	–	–	–	–	–	25	THN2262RDC
100A	NEMA Type 3R	–	–	–	–	–	–	25	THN2263RDC
30A	NEMA Type 4/4X	–	–	–	–	–	–	15	THN2261SSDC
60A	NEMA Type 4/4X	–	–	–	–	–	–	25	THN2262SSDC
100A	NEMA Type 4/4X	–	–	–	–	–	–	25	THN2263SSDC
30A	NEMA Type 5, 12	–	–	–	–	–	–	15	THN2261JDC
60A	NEMA Type 5, 12	–	–	–	–	–	–	25	THN2262JDC
100A	NEMA Type 5, 12	–	–	–	–	–	–	25	THN2263JDC

Three-pole, 480 and 600 Volts AC - 250 Volts DC or Two-pole with Switching Neutral, No Fuse

Ampere Rating	Enclosure Type	HP, 240 Vac, NEC Std, 1-ph	HP, 240 Vac, NEC Std, 3-ph	HP, 480 Vac, Time Delay, 3-ph	HP, 600 Vac, Time Delay, 3-ph	HP, 125 Vdc	HP, 250 Vdc	HP, 600 Vdc	Product Number
30A	NEMA Type 1	3	10	–	–	3	5	–	THN3321 ¹
30A	NEMA Type 1	3	10	20	30	3	5	–	THN3361
60A	NEMA Type 1	10	20	50	60	5	10	–	THN3362
100A	NEMA Type 1	20	40	75	100	–	20	–	THN3363
200A	NEMA Type 1	30	60	125	150	–	40	–	THN3364
400A	NEMA Type 1	–	125	250	350	–	50	–	THN3365
600A	NEMA Type 1	–	200	400	500	–	50	–	THN3366
800A	NEMA Type 1	–	–	–	–	–	–	–	TC36367 ^{2,3}
1200A	NEMA Type 1	–	–	–	–	–	–	–	TC36368 ^{2,3}
30A	NEMA Type 3R	3	10	20	30	3	5	–	THN3361R
30A	NEMA Type 3R	3	10	20	30	3	5	–	THN3361RF ⁴
60A	NEMA Type 3R	10	20	50	60	5	10	–	THN3362R
60A	NEMA Type 3R	10	20	50	60	5	10	–	THN3362RF ⁴
100A	NEMA Type 3R	20	40	75	100	–	20	–	THN3363R
200A	NEMA Type 3R	30	60	125	150	–	40	–	THN3364R
400A	NEMA Type 3R	–	125	250	350	–	50	–	THN3365R
600A	NEMA Type 3R	–	200	400	500	–	50	–	THN3366R
30A	NEMA Type 4/4X	3	10	20	30	3	5	–	THN3361SS ⁵
60A	NEMA Type 4/4X	10	20	50	60	5	10	–	THN3362SS ⁵
100A	NEMA Type 4/4X	20	40	75	100	–	20	–	THN3363SS ⁵
200A	NEMA Type 4/4X	30	60	125	150	–	40	–	THN3364SS ⁵
400A	NEMA Type 4/4X	–	125	250	350	–	50	–	THN3365SS
600A	NEMA Type 4/4X	–	200	400	500	–	50	–	THN3366SS
30A	NEMA Type 5, 12	3	10	20	30	3	5	–	THN3361J
60A	NEMA Type 5, 12	10	20	50	60	5	10	–	THN3362J
100A	NEMA Type 5, 12	20	40	75	100	–	20	–	THN3363J
200A	NEMA Type 5, 12	30	60	125	150	–	40	–	THN3364J
400A	NEMA Type 5, 12	–	125	250	350	–	50	–	THN3365J
600A	NEMA Type 5, 12	–	200	400	500	–	50	–	THN3366J

For Type 1 Enclosure: 200-600 amp devices available factory reversed for bottom feed. Add "B" suffix to product number (e.g., TH33365B). UL Listed.

For Type 3R Enclosure: 30-200 amp devices have removable closing cap. Order hubs for these devices separately on page 4-29. Larger amp devices require field cut openings and **customer-supplied** hub.

¹Rated 250 Vac/dc only. Compact enclosure.

²Rated 600 Vac only. Type HD electrical performance does not apply.

³Neutral kit not available. Not suitable for use as service equipment. Order TC72XXX series product numbers and separate neutral kit as required.

⁴Farm switch with oversize Type 3R enclosure and vertical hinge. See enclosure dimensions on page 4-31.

⁵Available with "BA" suffix for ARRA compliance. Same list price and GO schedule. Contact GE Sales Office for other ARRA compliant safety switches.

