

# CR151K Modular Resilient Terminal Blocks

300 and 600 Volts  
275 Amperes Maximum at 30°C Ambient  
Wire Sizes #22 to 2/0

## Ordering Information

Catalog Number represents one device. List price is per device. Devices are sold only in standard carton quantities. Order quantity of devices needed in increments of standard carton quantities.

Example: Order 200 quantity of CR151KFC @ **\$4.80 each, GO-10G5. Total List Price, \$960.00, GO-10G5.**

## Terminal Blocks, Fuseholders, Accessories

Subject to quantity discount. Refer to current **GO-10G5** discount schedule.

UL Recognized Amp Rating	Amperes <sup>①</sup> at 30°C	Description	Points Per Block	Wire Size	Accessories Ref. No. See Table Below	Catalog Number	Standard Carton Quantity	List Price GO-10G5
--------------------------	------------------------------	-------------	------------------	-----------	--------------------------------------	----------------	--------------------------	--------------------

### Basic Terminal Blocks: Box or "Collar-Type" Terminals: Rail Mounting<sup>③</sup>; 600 Volts, Except CR151KEC04E (300 Volts)

30	50	Compact, 1 inch	4	22-10	1, 2, 9, 10, 14, 21	CR151KFC04E	100	\$ 6.00
40	75	Compact, 1.17 inch	3	22-8	1, 2, 3, 5, 12, 14	CR151KFC	100	4.80
40	50	Compact, 0.94 inch	3	22-10	1, 2, 3, 14, 20, 21	CR151KFC43E	100	4.80
40	70	Compact, 5/8 inch	2	22-8	1, 2, 3, 4, 11, 14	CR151KFC02	100	3.60
70	130	Medium-duty, 5/8 inch	1	18-4	1, 2, 3, 6, 14	CR151KFC01D	100	3.60
90	130	Medium duty, 1 1/8 inch	3	18-2	1, 2, 3, 6, 14, 21	CR151KFC10C	24	10.65
175	270	Large cable, 3 1/8 inch	3	14-2/0	1, 2, 3, 14	CR151KFC10B	8	24.00

### Fuse Holder: Box or "Collar-Type" Terminals: Rail Mounting; 600 Volts

30	—	For 1 3/32 x 1 1/2-inch long fuse	1	22-8	1, 2, 3, 7, 8, 14, 21	CR151KCC01AM	50	5.86
----	---	-----------------------------------	---	------	-----------------------	--------------	----	------

### Disconnect: Fused or Nonfused; Box or "Collar-Type" Terminals; Rail Mounting

30	—	Isolating Disconnect	1	22-8	1, 2, 3, 7, 14, 21	CR151KGC01	20	5.85
30	—	Isolating Disconnect with holder for 1/4" Dia. by 1" to 1 1/16" long fuse	1	22-8	1, 2, 3, 7, 14, 21	CR151KHC01AN	20	8.40

### 12-Point Terminal Block (See Page 12-4 for Features and Mounting Instructions.)

20A at 300 V 5A at 600 V	—	12-Point Terminal Block	12	12-22	1, 2, 14, 16, 17, 21	CR151KFC45F	20	14.85
-----------------------------	---	-------------------------	----	-------	----------------------	-------------	----	-------

## Accessories<sup>④</sup>

Ref. No.	Description	Catalog Number	Standard Carton Quantity <sup>②</sup>	List Price, GO-10G5
1	Aluminum Mtg. Rail, 72-in.	CR151KX001	20	\$19.50
2	Stand-Off Channel, 72-in. <sup>⑤</sup>	CR151KX002	20	22.20
3	Marking Tape, 12 1/2-in.	CR151KX003	50	.38
4	Jumper, 2 pt., offset	CR151KX004	100	.45
5	Jumper, 2 pt.	CR151KX005	100	.45
6	Jumper, 2 pt.	CR151KX006	100	1.13
7	Jumper, 2 pt.	CR151KX007	100	.82
8	Fuse Puller (1 per holder)	CR151KX008	50	1.50
9	Jumper, 5 pt.	CR151KX009	100	1.05
10	Marking Tape, 6-in.	CR151KX010	50	.38
11	Marking Tab, one block	CR151KX011	100	.03
12	Marking Tab, one block	CR151KX012	100	.03
13	Molded Marking Tape, 12-in.	CR151KX013	25	1.65
14	Aluminum Mtg. Rail, 36-in.	CR151KX014	10	9.75
16	Jumper, 13 pt. (for KFC45F)	CR151KX016	100	1.30
17	Marking Strip (for KFC45F—enough for 30 blocks)	CR151KX017	1	10.15
20	Jumper, 2 pt.	CR151KX020	100	.60

Ref. No.	Description	Catalog Number	Standard Carton Quantity <sup>②</sup>	List Price, GO-10C2
21	DIN rail—35 mm (1 meter length)	CLXR35	1	\$8.00

- ① Maximum Amperes in 30°C ambient at terminal block—see chart, page 12-4, for other settings.
- ② Sold only in standard carton quantities: See ordering information above.
- ③ CR151KFC10C and CR151KFC10B are also base mountable.
- ④ See Accessories column in other tables to determine where items are used.
- ⑤ Use only with Mounting Rail, Ref. No. 1 or 14. Lubrication required on rail when mounting stand-off channel.