

Circuit Breaker Enclosures Hubs and Other Accessories

Section 4

Universal Raintight Hubs, Aluminum

For outdoor enclosures that have removable closing caps.

Nominal Conduit Diameter (in.)	Standard Package	Product Number	List Price GO-131A
3/4	10	TC75	\$24.00
1	10	TC100	\$24.00
1 1/4	10	TC125	\$24.00
1 1/2	10	TC150	\$24.00
2	10	TC200	\$40.25
2 1/2	10	TC250	\$67.75
3	5	TC300	\$100.00
Closing Cap	10	TCCP	\$2.60



TC150

Stainless Steel Cover

For flush mounted Type 1 circuit breaker enclosures, field installed only.

For Use with	Product Number	List Price GO-134
TE100F	TE100FSS	\$297.00
TF225F	Order by Description	\$114.00
TJ400F	Order by Description	\$151.00 ¹
TJ600F	Order by Description	\$286.00

¹GO-134A.

Insulated Groundable Neutrals

Max. Ampere Rating	Lug Wire Size (Cu-Al) AWG/kcmil	Standard Package	Product Number	List Price GO-134
100	14-1/0 Cu, 12-1/0Al	1	TNI100	\$80.50
225	1-300	1	TNIA225	\$98.50
400	(2) 1/0-250 or (1) 4-600	1	TNIA400	\$122.00
400	(2) 1/0-250 or (1) 4-600	1	TNIA400VG	\$122.00
600	(2) 2/0-500	1	TNIA600	\$180.00
600	(2) 2/0-500	1	TNIA600VG	\$180.00
800	(3) 250-500	1	TNIA800	\$297.00
800	(3) 250-350 Cu or (3) 250-500 Al	1	TNIA800G	\$297.00
1200	(4) 250-350 Cu or (4) 250-500 Al	1	TNIA1200	\$447.00
1200	(4) 250-350 Cu or (4) 250-500 Al	1	TNIA1200G	\$447.00
1200	(4) 250-400 Cu Only	1	TNIAC1200	\$447.00

Ground Kits

Ampere Rating	Product Number	List Price GO-137A
70-125 amp	TGL1	\$6.75
150-400 amp	(1) TGL1 plus (1) TGL20	\$6.75
600-1200 amp	TGL6	\$68.25 ²

²GO-131.

