




Nothing but **HEAVY DUTY.**

For the Longest Life, Look For:



Up to 50% Longer Life



**METAL CUTTING SAWZALL® BLADES**

Optimized for best cutting performance in pipe, conduit, strut, threaded rod, angle iron, duct and other metal building materials.



**LONG LIFE**

▪ Double relief angle reduces tooth stress



**FAST CUTTING**

▪ Precision forming process creates sharper teeth

Description	TPI	Length	Height	Width	5 Pack	25 Pack	50 Pack	Bulk Pack	Qty	Application
	10	4"	3/4"	0.035"	48-00-5090	-	-	-	-	1/4" - 3/8"
	10	6"	3/4"	0.035"	48-00-5092	-	48-01-6092	48-01-7092	100	1/4" - 3/8"
<b>THE TORCH™</b>	10	6"	1"	0.042"	48-00-5712	48-00-8712	-	48-01-7712	100	1/4" - 3/8"
<b>THE TORCH™ ice hardened</b>	10	6"	1"	0.042"	48-00-4712	-	-	48-01-9712	50	1/4" - 3/8"
<b>THE TORCH™</b>	10	9"	1"	0.042"	48-00-5713	48-00-8713	-	48-01-7713	100	1/4" - 3/8"
<b>THE TORCH™ ice hardened</b>	10	9"	1"	0.042"	48-00-4713	-	-	48-01-9713	50	1/4" - 3/8"
<b>THE TORCH™</b>	10	12"	1"	0.042"	48-00-5714	-	-	-	-	1/4" - 3/8"
	14	4"	3/4"	0.035"	48-00-5181	-	-	-	-	3/16" - 1/4"
	14	6"	3/4"	0.035"	48-00-5182	48-00-8182	48-01-6182	48-01-7182	100	3/16" - 1/4"
	14	6"	5/8"	0.035"	48-00-5282	-	48-01-6282	48-01-7282	100	3/16" - 1/4"
<b>ice hardened</b>	14	6"	3/4"	0.035"	48-00-4182	-	-	48-01-9182	50	3/16" - 1/4"
<b>THE TORCH™</b>	14	6"	1"	0.042"	48-00-5782	48-00-8782	-	48-01-7782	100	3/16" - 1/4"
<b>THE TORCH™ ice hardened</b>	14	6"	1"	0.042"	48-00-4782	-	-	48-01-9782	50	3/16" - 1/4"
	14	9"	3/4"	0.035"	48-00-5187	-	48-01-6187	48-01-7187	100	3/16" - 1/4"
<b>ice hardened</b>	14	9"	3/4"	0.035"	48-00-4187	-	-	48-01-9187	50	3/16" - 1/4"
<b>THE TORCH™</b>	14	9"	1"	0.042"	48-00-5787	48-00-8787	-	48-01-7787	100	3/16" - 1/4"
<b>THE TORCH™ ice hardened</b>	14	9"	1"	0.042"	48-00-4787	-	-	48-01-9787	50	3/16" - 1/4"
<b>THE TORCH™</b>	14	12"	1"	0.042"	48-00-5794	-	-	-	-	3/16" - 1/4"
	18	4"	3/4"	0.035"	48-00-5183	-	-	-	-	1/8" - 3/16"
	18	6"	3/4"	0.035"	48-00-5184	48-00-8184	48-01-6184	48-01-7184	100	1/8" - 3/16"
	18	6"	5/8"	0.035"	48-00-5284	-	48-01-6284	48-01-7284	100	1/8" - 3/16"
<b>ice hardened</b>	18	6"	3/4"	0.035"	48-00-4184	-	-	48-01-9184	50	1/8" - 3/16"
<b>THE TORCH™</b>	18	6"	1"	0.042"	48-00-5784	48-00-8784	-	48-01-7784	100	1/8" - 3/16"
<b>THE TORCH™ ice hardened</b>	18	6"	1"	0.042"	48-00-4784	-	-	48-01-9784	50	1/8" - 3/16"
	18	9"	3/4"	0.035"	48-00-5188	-	48-01-6188	48-01-7188	100	1/8" - 3/16"
<b>ice hardened</b>	18	9"	3/4"	0.035"	48-00-4188	-	-	48-01-9188	50	1/8" - 3/16"
<b>THE TORCH™</b>	18	9"	1"	0.042"	48-00-5788	48-00-8788	-	48-01-7788	100	1/8" - 3/16"
<b>THE TORCH™ ice hardened</b>	18	9"	1"	0.042"	48-00-4788	-	-	48-01-9788	50	1/8" - 3/16"
	18	12"	3/4"	0.035"	48-00-5189	-	48-01-6189	48-01-7189	100	1/8" - 3/16"
<b>ice hardened</b>	18	12"	3/4"	0.035"	48-00-4189	-	-	-	-	1/8" - 3/16"
<b>THE TORCH™</b>	18	12"	1"	0.042"	48-00-5789	48-00-8789	-	48-01-7789	100	1/8" - 3/16"
	24	4"	3/4"	0.035"	48-00-5185	-	-	-	-	Up to 1/8"
	24	6"	3/4"	0.035"	48-00-5186	48-00-8186	48-01-6186	48-01-7186	100	Up to 1/8"
	24	6"	5/8"	0.035"	48-00-5286	-	-	48-01-7286	100	Up to 1/8"
<b>ice hardened</b>	24	6"	3/4"	0.035"	48-00-4186	-	-	48-01-9186	50	Up to 1/8"

See the specialty SAWZALL® blade section for additional metal cutting options, including scrolling blades

CUTTING ACCESSORIES