

# HEAVY-DUTY WOOD BORING DRILL BITS

# HEAVY-DUTY SELFEED BIT KITS



### 7-BIT PLUMBERS' KIT

**49-22-0065** Complete assortment of the most commonly used MILWAUKEE bits for big hole drilling. Ouick change auger sizes include 7/8" (48-13-6552), 1-1/8" (48-13-6555), 1-1/4" (48-13-6557) auger bits and selfeed bits in 1-3/4", 2-1/8", 2-9/16" diameters. Also 5-1/2" one piece – shank and coupling – extension and carrying case.



#### 7-BIT CONTRACTORS' KIT

**49-22-0130** Complete assortment of the most commonly used MILWAUKEE selfeed bits for big hole drilling. Sizes include 1", 1-1/8", 1-1/4", 1-1/2", 1-3/4", 2-1/8", 2-1/8", 2-9/16" diameters. Also 5-1/2" one piece – shank and coupling – extension and carrying case.



#### 4-BIT CONTRACTORS' KIT

**49-22-0135** Assortment of MILWAUKEE selfeed bits for big hole drilling. Sizes include 1-3/8", 1-1/2", 2-1/8", 2-9/16" diameters. Also 5-1/2" one piece – shank and coupling – extension and carrying case.

### SELFEED BIT KIT - CASE ONLY

Case is made of hi-impact polyethylene double wall con-struction for full bit protection. (No metal to metal contact!)

PLUMBERS' KIT CASE: 48-55-0790

CONTRACTORS' KIT CASE (4 OR 7 BIT): 48-55-0775

# HEAVY-DUTY AUGER & SHIP AUGER BITS

Sizes from 3/4" to 1-1/2"...All 4" twist and 6-1/2" long. 7/16" hex quick change shanks for sure chuck grip. Feed screw pilot draws bit into wood. Sharp cutting spurs and lips can be quickly resharpened for fast, efficient production. Hardened alloy steel protect against damage in nail imbedded wood.

For all types of wood frame construction. Hardened alloy steel for long life in the nail imbedded wood. Precision machined for smooth, wobble free boring. Large, wide throat design gives excellent chip removal. Self feeding screw point and 7/16" hex quick change shank. Impact wrenches featuring a quick change chuck and 1/2" D-Handle drills and larger can use all 1/2 7/16" shank bits.



## 6-1/2" AUGER BITS

SHANK	DIA.	CATALOG NUMBER	OVERALL LENGTH	FOR STD. PIPE Sizes
7/16" Hex	3/4"	48-13-0750	6-1/2"	
7/16" Hex	7/8"	48-13-0870	6-1/2"	3/8"
7/16" Hex	1"	48-13-1000	6-1/2"	
7/16" Hex"	1-1/8"	48-13-1120	6-1/2"	1/2"
7/16" Hex	1-1/4"	48-13-1250	6-1/2"	3/4"
7/16" Hex	1-3/8"	48-13-1370	6-1/2"	
7/16" Hex"	1-1/2"	48-13-1500	6-1/2"	1"



### **6" SHIP AUGER BITS**

SHANK	DIA.	CATALOG NUMBER	OVERALL LENGTH
7/16" Hex	11/16"	48-13-0683	6"
7/16" Hex	3/4"	48-13-0753	6"
7/16" Hex	13/16"	48-13-0813	6"
7/16" Hex	7/8"	48-13-0873	6"
7/16" Hex	15/16"	48-13-0933	6"
7/16" Hex	1"	48-13-1003	6"
7/16" Hex	1-1/16"	48-13-1063	6"
7/16" Hex	1-1/8"	48-13-1123	6"
7/16" Hex	1-1/4"	48-13-1253	6"
7/16" Hex	1-3/8"	48-13-1373	6"
7/16" Hex	1-1/2"	48-13-1503	6"

18" SHIP AUGER BITS				
SHANK	DIA.	CATALOG NUMBER	OVERALL LENGTH	
7/16" Hex	9/16"	48-13-5560	18"	
7/16" Hex	5/8"	48-13-5620	18"	
7/16" Hex	11/16"	48-13-5680	18"	
7/16" Hex	3/4"	48-13-5750	18"	
7/16" Hex	13/16"	48-13-5810	18"	
7/16" Hex	7/8"	48-13-5870	18"	
7/16" Hex	15/16"	48-13-5930	18"	
7/16" Hex	1"	48-13-6000	18"	
7/16" Hex	1-1/16"	48-13-6010	18"	
7/16" Hex	1-1/8"	48-13-6120	18"	
7/16" Hex	1-1/4"	48-13-6250	18"	
7/16" Hex	1-3/8"	48-13-6370	18"	
7/16" Hex	1-1/2"	48-13-6500	18"	

# HEAVY-DUTY ELECTRICIAN'S BITS



A fast spiral, two flute – six inch twist, self feeding bit with an overall length of 8-1/2" for any tradesman needing a smooth, clean hole 5/8" to 1-1/4". 5/8" to 1" diameter bits have a 5/16" hex shank and 1-1/8" to 1-1/4" diameter bits have a 7/16" hex shank.

h	DIAMETER	CATALOG NUMBER	OVERALL LENGTH	CATALOG DIAMETER	OVERALL NUMBER	LENGTH
ן מ	5/8"	48-13-8062	8-1/2"	7/8"	48-13-8087	8-1/2"
a r	11/16"	48-13-8068	8-1/2"	1"	48-13-8100	8-1/2"
0	3/4"	48-13-8075	8-1/2"	1-1/8"	48-13-8112	8-1/2"
•	13/16"	48-13-8081	8-1/2"	1-1/4"	48-13-8125	8-1/2"