



5-3/8" 30 Teeth Ferrous Metal Circular Saw Blade

48-40-4070



What's Included

(1) 5-3/8" 30 Teeth Ferrous Metal Circular Saw Blade
(48-40-4070)

Features

- Dry - No lubricant required, saving time and money with less mess
- Cool - No extreme heat buildup preserves blade life and allows handling the work piece immediately
- Clean - No burrs eliminates secondary operations saving time and money
- Lasts up to 25x longer than abrasive blades

Overview

MetalTech™ circular saw blades were specifically designed to exceed the expectations of contractors for blade life, cut quality, and speed in the most demanding metal cutting applications – without a lubricant. A hand-tensioned, hardened alloy steel body extends blade life and delivers the highest quality cuts available. Carbide tipped teeth with Alternate Top Bevel grind shear through metal leaving burr-free, cool-to-touch cuts. Designed for use with the M18™ Cordless 5-3/8" Metal Saw, these blades feature a thin kerf that reduces the amount of drag and resistance while cutting, resulting in more cuts per charge.

Model Options

Item/Cat #	Diameter	Arbor Size	Number of Teeth	
48-40-4005	6-1/2"	5/8"	60	FIND RETAILERS
48-40-4006	6-7/8"	20mm	52	FIND RETAILERS
48-40-4015	6-1/2"	5/8"	48	FIND RETAILERS
48-40-4016	6-7/8"	20mm	36	FIND RETAILERS
48-40-4070	5-3/8"	20mm	30	FIND RETAILERS
48-40-4075	5-3/8"	20mm	50	FIND RETAILERS

Specifications

Pack Qty	1
Diameter	5-3/8"
Arbor Size	20mm
Number of Teeth	30

Item/Cat #	Diameter	Arbor Size	Number of Teeth	
48-40-4505	14"	1"	72	FIND RETAILERS
48-40-4510	14"	1"	90	FIND RETAILERS
48-40-4515	8"	5/8"	42	FIND RETAILERS
48-40-4520	8"	5/8"	50	FIND RETAILERS
48-40-4530	8"	5/8"	60	FIND RETAILERS
48-40-4540	8"	5/8"	60	FIND RETAILERS

[View Mobile Site](#)

© 2014 by Milwaukee Electric Tool Corporation. All rights reserved. |||