



HACKZALL™ BLADES

MATERIAL	BLADE LENGTH	TPI	ITEM PACK NO.
Wood Scroll	3-1/2"	10	49-00-5310
Metal Scroll	3-1/2"	24	49-00-5324
Fiberglass	4"	GRIT	49-00-5400
Multi-Material	4"	10	49-00-5410
PVC	4"	14	49-00-5414
PVC	6"	14	49-00-5614
EMT	4"	18	49-00-5418
Duct	4"	24	49-00-5424
Wood	4"	6	49-00-5460
Plaster	4"	6	49-00-5461
Wood/EMT/PVC/Duct	SET	MIX	49-22-0220



UP TO **35%***
MORE CUTS PER CHARGE
IN THE HACKZALL™ TOOL



* Versus a standard Sawzall™ Blade

BI-METAL BANDSAW BLADES

BLADE LENGTH	TPI	ITEM NO. 1 PACK	ITEM NO. 2 PACK	ITEM NO. 3 PACK	ITEM NO. 100 PACK	DIAMETER / WALL THICKNESS	APPLICATION
44-7/8"	10	48-39-0500	-	48-39-0501	48-39-0502	5/16" & Up	High speed cutting of aluminum, angle iron, bronze, brass, copper, galvanized pipe & mild steel.
44-7/8"	14	48-39-0510	48-39-0514	48-39-0511	48-39-0512	3/16" to 5/16"	
44-7/8"	18	48-39-0520	48-39-0524	48-39-0521	48-39-0522	5/32" to 3/16"	Slow speed cutting of tougher steels: stainless, chrome, tungsten steel.
44-7/8"	24	48-39-0530	48-39-0534	48-39-0531	48-39-0532	Up to 5/32"	
44-7/8"	10/14	48-39-0550	48-39-0554	48-39-0551	48-39-0552	3/16" to 1/2"	Interrupted cutting applications: tubing, structurals, etc
44-7/8"	14/18	48-39-0560	-	48-39-0561	48-39-0562	5/32" to 5/16"	

NEW! COMPACT BI-METAL BANDSAW BLADES

BLADE LENGTH	TPI	ITEM NO. 1 PACK	ITEM NO. 2 PACK	ITEM NO. 3 PACK	ITEM NO. 100 PACK	DIAMETER / WALL THICKNESS	APPLICATION
35.395"	10	48-39-0508	-	48-39-0509	48-39-0507	5/16" & Up	High speed cutting of aluminum, angle iron, bronze, brass, copper, galvanized pipe & mild steel.
35.395"	14	48-39-0518	-	48-39-0519	48-39-0517	3/16" to 5/16"	
35.395"	18	48-39-0528	-	48-39-0529	48-39-0527	5/32" to 3/16"	Slow speed cutting of tougher steels: stainless, chrome, tungsten steel.
35.395"	24	48-39-0538	-	48-39-0539	48-39-0537	Up to 5/32"	