

5/8" SDS Plus Rotary Hammer Kit

2416-22XC (2416-20 Tool-Only)

Specifications: RPM 0 - 900BMP 0 - 6,200

SDS Plus Chuck Type 2 Mode Operation Rotary Hammer and Rotation Only 10" Length

Includes: (2) M12™ REDLITHIUM™ XC4.0 Extended Capacity
Battery Packs, Charger, Carrying Case
Compatible with Social



SDS

1/2" SDS Plus Rotary Hammer Kit

2412-22XC (2412-20 Tool-Only)

Specifications:

-	rLU3 /
RPM	0 - 800
BPM	0 – 5,350
Chuck Type	SDS Plus
2 Mode Operation	Rotary Hammer and Rotation Only
Length	9"
Weight	3.9 lbs

Includes: (2) M12™ REDLITHIUM™ XC Extended Capacity Battery Packs, Charger, Carrying Case

Compatible with 2306-22 M12™ HAMMERVAC™ Universal Dust Extractor

M12™ Palm Nailer Kit

Hand Strap, Charger, Soft Carrying Case

13

2458-21 (2458-20 Tool-Only)

Specifications:			
	Impact Energy	2.2 ft-lbs (3.0J)	
	BPM	0 – 2,700	
	Collet Capacity	6D - 16D	
	Head	3/4" Low Profile	
	Magnetic Tip	Yes	
	Weight	3.4 lbs	

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack,



M12™ HAMMERVAC™ **Universal Dust Extractor**

2306-22 (2306-20 Tool-Only)



INDUSTRY'S ONLY UNIVERSAL DUST EXTRACTOR



Specifications:	
Universal Handle System	Compatible with Major Brands of SDS Plus Rotary Hammers and AC & DC Hammer Drills
Replaceable Certified HEPA Filter	Filters 99.97% of Debris 0.3 Microns and Above
Self-Powered by M12™ REDLITHIUM™ Battery Pack	No Cords or Hoses for Maximum Portability
3-Mode Switch	Yes (Auto-on and Auto-off w/Delay)
Max Bit Size	5/8"
Weight	3.3 lbs

Includes: (2) M12[™] REDLITHIUM[™] Compact Battery Packs, (3) Side Handle Collars, Side Handle Grip, Nozzle, Charger, Carrying Case



M12™ Rotary Tool Kit

2460-21 (2460-20 Tool-Only)

Specifications:

P	
Speed Settings	6
RPM	5,000 – 32,000
Collet	1/8", Universal
Length	9-1/2"
Weight	1.3 lbs

Includes: (1) M12[™] REDLITHIUM[™] Compact Battery Pack, (5) Cutting Wheels, (1) Mandrel, (1) Wrench, Charger, Soft Carrying Case

Related Accessory: 49-94-1500 – 5 Pc Reinforced Cut-Off Wheels





M12™ HACKZALL® **Recip Saw Kit**

2420-22, 2420-21 (2420-20 Tool-Only)

Specifications:

-	
SPM	0 – 3,000
Stroke Length	1/2"
Blade Clamp	QUIK-LOK® (Accepts all SAWZALL® Blades)
Length	11"
Weight	2.6 lbs

Includes: 2420-22 (2) M12™ REDLITHIUM™ Compact Battery Packs, (2) HACKZALL® Blades, Charger, Contractor Bag; 2420-21 Includes (1) M12™ REDLITHIUM™ Compact Battery Pack



M12™600 MCM Cable Cutter Kit

2472-21XC (2472-20 Tool-Only)

Specifications:

600 MCM Copper, 750 MCM Aluminum, 1-3/16" Communication Cable

Jaw Opening 1-7/16" Two-Speed Yes Length 10-1/2" Weight 6.9 lbs

Includes: (1) M12™ REDLITHIUM™XC Extended Capacity Battery Pack, Multi-Voltage Charger, Carrying Case **Related Accessory:** 48-44-0410 - M12[™] 600 MCM Cable Cutter Blade

M12™ Multi-Tool Kit

2426-22, 2426-21 (2426-20 Tool-Only)

Specifications:

-		
Speed Settings	12	
OPM	5,000 - 20,000	19 (66)
Universal Accessory Adapter	Yes	10
Length	10-7/8"	
Weight	2.1 lbs	

Includes: 2426-22 (2) M12[™] REDLITHIUM[™] Compact Battery Packs, (1) Accessory Adapter, (1) Wood Cutting Blade, (1) Sanding Pad, (5) Assorted Sanding Sheets, Charger, Contractor Bag; 2426-21 Includes (1) M12[™] REDLITHIUM[™] Compact Battery Pack



Specifications: SPM 0 - 2.800

Stroke Length 3/4" Bevel Capacity 45° (Positive Locks at 90° and 45°) QUIK-LOK® T-Shank Blade Clamp 8-3/4" Lenath Weight 4.2 lbs

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, (1) Milwaukee® 10 TPI Wood Cutting T-Shank Jig Saw Blade, (1) Anti-Splintering Insert, (1) Non-Marring Shoe, Charger, Contractor Bag



M12™ Sub-Compact **Band Saw Kit**

2429-21XC (2429-20 Tool-Only)

Specifications:		
SFPM	280	
Blade Size	27"	
Cut Capacity	1-5/8" x 1-5/8"	
Length	12"	
Weight	6.7 lbs	

Requirements. Suitable for One-Handed Use.

Includes: (1) M12[™] REDLITHIUM[™] XC Extended Capacity Battery Pack, (1) 18 TPI Sub-Compact Portable Band Saw Blade, Charger, Carrying Case

Related Accessory: 48-39-0572 - 18 TPI Sub-Compact Portable Band Saw Blades (3 Pack)





M12™ Copper **Tubing Cutter Kit**

2471-22, 2471-21 (2471-20 Tool-Only)

Specifications:

Cut Capacity	3/8" - 1" (1/2" - 1-1/8" U.D.)
Tubing Type	M, L, and K Copper
RPM	500
Length	14"
Weight	3.2 lbs



Includes: 2471-22 (2) M12™ REDLITHIUM™ Compact Battery Packs, Charger, Carrying Case; **2471-21** Includes (1) M12[™] REDLITHIUM[™] Compact Battery Pack


Related Accessory: 48-38-0010 - Copper Cutter Wheel (2 Pack)

M12™ PVC Shear Kit

2470-21 (2470-20 Tool-Only)



	- (/
Torque	1,900 in-lbs
Blade	3mm Reinforced Stainless Steel
Length	14-3/8"
Weight	4.7 lbs



Related Accessory:



M12™ ProPEX® **Expansion Tool Kit**

2432-22 (2432-20 Tool-Only)

Specifications:

Capacity	3/8" - 1"
Stroke Length	14mm
Speed	60 SPM
Head Compatibility	3/8" - 1" M12™ / Uponor
Head Rotation	Built-in Auto Rotator

Includes: (2) M12™ REDLITHIUM™ Compact Battery Packs, (1) 1/2" Expansion Head, (1) 3/4" Expansion Head, (1) 1" Expansion Head, Grease, Charger, Carrying Case

M12™ ProPEX® **Accessory Heads**

Sizes:		iii 🕶
49-16-2403	M12 [™] 3/8" Expansion Head	
49-16-2404	M12™ 1/2" Expansion Head	_
49-16-2405	M12 [™] 5/8" Expansion Head	
49-16-2406	M12™ 3/4" Expansion Head	
49-16-2408	M12™ 1" Expansion Head	

Compatible with both M12[™] and M18[™] ProPEX[®] Expansion Tools, and most Uponor Tools

ProPEX® is a registered trademark of Uponor, Inc.



M12™ FORCE LOGIC™ **Press Tool Kit**

2473-22 (2473-20 No Jaw Kit)

Spe	cifications	•=

Capacity	1/2" - 1-1/4" CU
Calibration Interval	32,000 Cycles (LED Indicator)
Approximate Cycle Time	5 Seconds
Press Force	5,400 lbs
Length	12-3/4"
Weight	3.8 lbs

Includes: 2473-22 (2) M12[™] REDLITHIUM[™] Compact Battery Packs, (3) Jaws 1/2" - 1", Charger, Carrying Case; 2473-20 Includes No Jaws

M12™ FORCE LOGIC™ Jaws

Sizes:

49-16-2450	M12™ 1/2" Compact Jaw
49-16-2451	M12™ 3/4" Compact Jaw
49-16-2452	M12™ 1" Compact Jaw
49-16-2453	M12™ 1-1/4" Compact Jaw

Designed for use with all major fitting manufacturers Jaws compatible with 2473-20 M12™ Press Tool



M12™ No-Hub **Driver Kit**

2455-22 (2455-20 Tool-Only)

Specifications:

Torque Settings	60 in-lbs / 80 in-lbs / Drill Mode
RPM	0 – 750
Chuck Type	1/4" Hex
Calibration Interval	25,000 Cycles (LED Indicator)
Weight	2.7 lbs

Includes: (2) M12™ REDLITHIUM™ Compact Battery Packs. (3) SHOCKWAVE™ Nut Drivers (1/4", 5/16", 3/8"), Charger, Carrying Case



M12™ 10 oz Caulk and **Adhesive Gun Kit**

2441-21 (2441-20 Tool-Only)

Specifications:

Force	400 lbs
Inches Per Minute	0 – 29
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	4.1 lbs

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, (1) 10 oz Carriage, (1) M12™ Plunger Rod and Piston Assembly, Charger



M12™ Caulk Gun Accessories

48-08-0900 M12[™] 10 oz Caulk and Adhesive Gun Conversion Kit

48-08-0905 M12[™] 20 oz Aluminum Barrel Sausage Style Caulk and Adhesive Gun Conversion Kit



48-08-0910 M12™ Quart Caulk and Adhesive Gun Conversion Kit



48-08-1091 20 oz Aluminum Barrel Kit



48-08-1096 20 oz Clear Barrel Kit



31-12-0700 Caulk Gun Nozzle - Black



M12[™] 20 oz Aluminum Barrel Sausage **Style Caulk and Adhesive Gun Kit**

2442-21 Specifications:




Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, (1) 20 oz Aluminum Sausage Style Barrel, (1) M12™ 20 oz Plunger Rod and Piston Assembly, Nozzle, Charger



Output Pressure Over 8,000 PSI Run-Time

Weight



Includes: (1) M12[™] REDLITHIUM[™] XC Extended Capacity Battery Pack, (1) 36" Flex Hose with Spring Guard, (1) Grease Coupler, Charger, Carrying Case





2444-21

Specifications:

Force	400 lbs
Inches Per Minute	0 – 29
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	5.5 lbs



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, (1) Quart Carriage, (1) M12[™] Quart Plunger Rod and Piston Assembly, Charger



M12™ M-SPECTOR 360™ **Rotating Inspection** Scope

2313-21 (2313-20 Tool-Only)

Specifications:

Screen Size	2.7 High-Resolution LCD
Display Resolution	320 x 240
Camera Head Diameter	9mm (0.35")
Cable Length	3'
LED Brightness	4 LEDs, 5 Settings

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Hook, Magnet, Mirror Attachments, Charger, Carrying Case

M12™ M-SPECTOR 360™ 9 ft Rotating Inspection **Scope Kit**

2314-21

Specifications:

Screen Size	2.7" High-Resolution LCD
Display Resolution	320 x 240
Camera Head Diameter	9mm (0.35")
Cable Length	9'
LED Brightness	4 LEDs, 5 Settings

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack. Hook, Magnet, Mirror Attachments, Pipe Guide, Charger, Carrying Case



M12™ M-SPECTOR™ AV **Multimedia Camera Kit** (17mm) 2311-21

Specifications:

opoomoutono.			
Screen Size	3.5" LCD		
Display Resolution	320 x 240		
Camera Head Diameter	17mm (0.7")		
Cable Length	3'		
Adjustable Image Zoom	4X		
LED Brightness	4X		

Includes: (1) M12[™] REDLITHIUM[™] Compact Battery Pack, 17mm Camera Cable, 2GB Memory Card, USB Cable, Charger, Carrying Case

M12™ M-SPECTOR™ AV **Multimedia Camera Kit** (9mm) 2312-21

Specifications:

opcomoditoris:			
Screen Size	3.5" LCD		
Display Resolution	320 x 240		
Camera Head Diameter	9mm (0.35")		
Cable Length	3'		
Adjustable Image Zoom	4X		
LED Brightness	4X		





M12™ M-SPECTOR 360™ Accessories

Items: 48-53-0112	Accessory 3-Pack (Includes Hook, Mirror, Magnet Attachment)	1
48-53-0113	Pipe Guide Accessory	-

M12™ M-SPECTOR™ AV Accessories

items:		
48-53-0125	(17mm) AV 3' Replacement Digital Camera Cable	
48-53-0130	(9mm) AV 3' Replacement Analog Camera Cable	
48-53-0141	AV 3' Extension Cable	6
48-53-0140	AV 8' Extension Cable	0

M12[™] 160x120 **Thermal Imager**

2260-21, NIST Certified 2260-21NST

Specifications:

specifications.		
Thermal Resolution	160 x 120	
Temperature Range	14° to 662° F (-10° to	350° C
Temperature Accuracy	±2% (±2° C)	
Color Palettes	Iron, Rainbow, Gray	
Visual Camera	Yes	
Screen Size	3.5" LCD	

Includes: (1) M12[™] REDLITHIUM[™] Compact Battery Pack, Thermal Imager Report Software, 2GB SD Card, (1) USB Cable, (1) SD Card Reader, Quick Reference Card, Statement of Calibration, Charger, Carrying Case





Hands Free

49-24-0146

Specifications:

Light Type LED Lumens 86 Integrated Magnet Head Rotation 90°

M12™ LED Work Light

Battery and Charger Sold Separately



M12™ LASER TEMP-GUN™ **Thermometer Kit**

2276-21, NIST Certified 2276-21NST (2276-20, 2276-20NST Tool-Only)

Specifications:

- T D	000 +- 1 4700 F	000 t- 0000 O)	Sheete C
Temperature Range	-22° to 1,472° F (-30° to 800° C)	
Temperature Accuracy	1.5%		
Distance to Spot	40:1		4
Contact Temperature Range	-40° to 1,022° F (-40° to 550° C)	
Ambient Humidity / Dew Point Measurement	No	TOOL	BATTERY
Display Resolution	0.1° C, 0.1° F	YEAR WAR	YEAR
		(HAIII	тм

Includes: (1) M12[™] REDLITHIUM[™] Compact Battery Pack, (1) K-Type Thermocouple, Manual, Charger, Carrying Case


M12™ LASER TEMP-GUN™ Thermometer for HVAC/R Kit

2277-21, NIST Certified 2277-21NST (2277-20, 2277-20NST Tool-Only)

Specifications:

,	specifications:			
	Temperature Range	-22° to 1,472° F (-30° to 80	00° C)	Shape =
	Temperature Accuracy	1.5%		
	Distance to Spot	40:1		
	Contact Temperature Range	-40° to 1,022° F (-40° to 55	50° C)	
	Ambient Humidity / Dew Point Measurement	Yes	TOOL B	
	Display Resolution	0.1° C, 0.1° F	WARRA	YEAR

Includes: (1) M12[™] REDLITHIUM[™] Compact Battery Pack, (1) K-Type Thermocouple, Manual, Charger, Carrying Case



M12™ SUB-SCANNER™ **Detection Tool Kit**

2291-21 (2291-20 Tool-Only)

Specifications:

specifications:	
Detects Rebar in Concrete	Yes
Depth (Metal)	6"
Ferrous / Non-Ferrous Differentiation	Yes
Depth (Stud)	1-1/2"
Stud Edges & Center	Yes
Push-Button Calibration	Yes



M12™ LED Stick Light

2351-20

Specifications:

Light Type	LED
Lumens	220
Hands Free	Multi-Position Stainless Steel Hook
Length	9-1/4"
Weight	0.6 lbs

Battery and Charger Sold Separately

Related Accessory:

49-24-2351 – M12[™] Stick Light Magnet Compatible with Milwaukee[®] M12[™]LED Stick Light (2351-20). Holds light to metal surfaces for hands free use.

M12™ 2-Beam **Plumb Laser Kit**

2320-21 (2320-20 Tool-Only)

Specifications:

Accuracy	1/4" at 100'
Leveling Range	±4°
Laser Power	<1mW
Out of Level Indicator	Yes
Magnetic Base	Yes

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger, Carrying Case



M12™ Tool Holster

2335-20

Specifications:

Material	Heavy Duty Nylon
On-Board Bit Storage	Yes
Weight	0.3 lbs

Designed to fit most M12™ Drilling and Fastening Tools



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, 9mm Camera Cable, 4GB Memory Card, USB Cable, Charger, Carrying Case

REDLITHIUM™ 2.0/XC4.0

- Up to 2X More Run-Time
- Up to 20% More Power
- Over 2X More Recharges



M12™ REDLITHIUM™ 2.0 **Battery Pack** 48-11-2420

Specifications:

Cell Chemistry LITHIUM-ION 45 minutes Charge Time

M12™ REDLITHIUM™ XC4.0 Battery Pack 48-11-2440

Specifications:

Amp Hours	4.0
Cell Chemistry	LITHIUM-ION
Charge Time	90 minutes



REDLITHIUM™ RUN-TIME ADVANTAGE

REDI	ITHIU	M™ XC4.0				
REDI	ITHIU	M™ XC				
			Standa LITHIU	ard High C M-ION	apacity	
REDI	ITHIU	M™ 2.0				

REDLITHIUM[†]

M12™ REDLITHIUM™ **Compact Battery Pack**

48-11-2401

Specifications:

-	
Amp Hours	1.5
Cell Chemistry	LITHIUM-ION
Charge Time	30 minutes







M12™ Jobsite Radio

2590-20

Specifications:

Tuner	Digital Reception with Signal Processor
Modes	AM/FM/AUX
Weight	3.5 lbs
Auxiliary Input	1/8" Stereo Jack
Powered By	All M12™ Batteries / AC Adapter



Batteries Sold Separately

Includes: (1) Auxiliary Input Cord, (1) AC Adapter, (2) AAA Batteries (for memory backup)

M12™ Power Source

49-24-2310

Specifications:

On-Board Fuel Gauge	Yes
Powered By	All M12™ Batteries
2.1 Amp USB Port	Universal Charging for Smart Phones, Tablets, and Other Portable Electronic Devices

Batteries Sold Separately

Powers all Milwaukee® M12™ Heated Gear







M12™ LITHIUM-ION Battery Charger*

48-59-2401

Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes





M12™ AC/DC Wall & Vehicle Charger*

2510-20

Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes
*Compatible with All M12™ Batte	rios



M12™ REDLITHIUM™ XC Extended **Capacity Battery Pack**

48-11-2402

Specifications:

Amp Hours	3.0	
Cell Chemistry	LITHIUM-ION	
Charge Time	60 minutes	





M12[™] and M18[™] **Multi-Voltage Charger**

48-59-1812

Specifications:

-	
Compatibility	All M12 [™] and M18 [™] Batteries
Charge Sequence	Sequential (First In, First Charged)
Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes

Batteries Sold Separately

M12™ Heated Jacket Kit - Red

2341 (2340 Jacket-Only)

Specifications:

-	
Heat Zones	5 (Chest, Back, Pockets)
Heat Settings	3 Per Zone (High, Medium, Low)
Jacket Material	100% Polyester
Water / Wind Resistant	Yes
USB Charger	Yes
Run-Time	Up to 6 Hours

Includes: (1) M12[™] REDLITHIUM[™] Compact Battery Pack, (1) M12™ Power Source, Charger

Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ Heated Jacket Kit - Black

2345 (2344 Jacket-Only)

Specifications:

•	
Heat Zones	5 (Chest, Back, Pockets)
Heat Settings	3 Per Zone (High, Medium, Low)
Jacket Material	100% Polyester
Water / Wind Resistant	Yes
USB Charger	Yes
Run-Time	Up to 6 Hours

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, (1) M12[™] Power Source, Charger

Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ Heated Jacket Kit Realtree Xtra® Camouflage

2343 (2342 Jacket-Only)

Specifications:	₩
Heat Zones	5 (Chest, Back, Pockets)
Heat Settings	3 Per Zone (High, Medium, Low)
Jacket Material	Soft-Shell Fabric Blend for Reduced Noise During Movement
Water / Wind Resistant	Yes
USB Charger	Yes
Run-Time	Up to 6 Hours


Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, (1) M12™ Power Source, Charger

Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ High Visibility **Heated Jacket Kit**

2347 (2346 Jacket-Only)

Specifications:



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger Available Sizes: Medium, Large, XL, 2X, 3X, 4X

M12™ Heated Jacket 12V **DC Plug Adapter**

49-24-2301



M18[™] Power Source

49-24-2371

Batteries Sold Separately



2371 (2370 Hoodie-Only)

Specifications:

Heat Zones	3 (Chest, Back)
Heat Settings	3 Per Zone (High, Medium, Low)
Hoodie Material	Cotton/Polyester Blend
Water / Wind Resistant	No
Washer / Dryer Safer	Yes
Run-Time	Up to 6 Hours

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ Heated Hoodie Kit - Gray

2373 (2372 Hoodie-Only)

Specifications:

Heat Zones	3 (Chest, Back)
Heat Settings	3 Per Zone (High, Medium, Lov
Hoodie Material	Cotton/Polyester Blend
Water / Wind Resistant	No
Washer / Dryer Safer	Yes
Run-Time	Up to 6 Hours

Includes: (1) M12[™] REDLITHIUM[™] Compact Battery Pack, Charger Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ Heated Hoodie Kit - Khaki

2375 (2374 Hoodie-Only)

Specifications:

Heat Zones	3 (Chest, Back)
Heat Settings	3 Per Zone (High, Medium, Lov
Hoodie Material	Cotton/Polyester Blend
Water / Wind Resistant	No
Washer / Dryer Safer	Yes
Run-Time	Up to 6 Hours

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ High Visibility Heated Hoodie Kit

2377 (2376 Hoodie-Only)

Specifications:

Heat Zones	3 (Chest, Back)
Heat Settings	3 Per Zone (High, Medium, Low)
Hoodie Material	ANSI Class II 100% Polyeste
Water / Wind Resistant	Yes
Washer / Dryer Safer	Yes (Up to 25 Washes)
Run-Time	Up to 6 Hours

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ Heated Hand Warmers

Realtree Xtra® Camouflage 2321-21 (2321-20 Hand Warmer-Only Black 2322-21 (2322-20 Hand Warmer-Only)

Specifications:

Heat Zones	2 (Front, Back)
Heat Settings	3 Per Zone (High, Medium, Low)
Hand Warmer Material	100% Polyester
Water / Wind Resistant	Yes
Adjustable Buckle-Strap	Yes

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger Available Sizes: One Size Fits Most

Realtree Xtra © 2012 of Jordan Outdoor Enterprises 1 td. all rights reserved