

**5 Choose the Blade Profile**

**A) DEMOLITION BLADES:**

**MAXIMUM DURABILITY**

- A thicker, more rigid blade body resists fracturing and bending

**STRAIGHTER CUTS**

- The 1" tall blade body reduces blade twisting for straighter, more accurate cuts



**B) STANDARD BLADES:**

- Traditional blade thickness and profile



**C) SCROLL CUTTING BLADES:**

- Low profile for tight contour cutting



**WOOD CUTTING SAWZALL® BLADES**

Optimized for best cutting performance in nail-embedded dimensional lumber, OSB, plywood and other engineered lumbers.



**FAST CUTTING**

- Precision forming process creates sharper teeth



**EASY PLUNGING**

- Full raker tooth on blade tip

Description	TPI	Length	Height	Width	5 Pack	25 Pack	50 Pack	Bulk Pack	Qty	Application
	6	6"	3/4"	0.050"	48-00-5035	-	48-01-6035	48-01-7035	100	
<b>THE AX™</b>	5/8	6"	1"	0.062"	48-00-5021	48-00-8021	-	48-01-7021	100	
	6	9"	3/4"	0.050"	48-00-5036	48-00-8036	48-01-6036	48-01-7036	100	
<b>THE AX™</b>	5/8	9"	1"	0.062"	48-00-5026	48-00-8026	-	48-01-7026	100	
	6	12"	3/4"	0.050"	48-00-5037	-	48-01-6037	48-01-7037	100	
<b>THE AX™</b>	5/8	12"	1"	0.062"	48-00-5027	48-00-8027	-	48-01-7027	100	

See the specialty SAWZALL® blade section for additional wood cutting options, including 4/6 TPI scrolling blades

**GENERAL PURPOSE SAWZALL® BLADES**

Designed for versatile cutting performance across the broadest selection of materials including nail-embedded wood, plastics, ferrous and non-ferrous metals.



**LONG LIFE**

- Double relief angle reduces tooth stress



**FAST CUTTING**

- Precision forming process creates sharper teeth

Description	TPI	Length	Height	Width	5 Pack	25 Pack	50 Pack	Bulk Pack	Qty	Application
	8/12	6"	3/4"	0.050"	48-00-5091	-	48-01-6091	48-01-7091	100	
	8/12	6"	3/4"	0.050"	48-00-4091	-	-	48-01-9091	50	
<b>THE WRECKER™</b>	8	6"	1"	0.062"	48-00-5701	48-00-8701	-	48-01-7701	100	
	8/12	8"	3/4"	0.050"	48-00-5093	48-00-8093	48-01-6093	48-01-7093	100	
	8/12	8"	3/4"	0.050"	48-00-4093	-	-	48-01-9093	50	
<b>THE WRECKER™</b>	8	9"	1"	0.062"	48-00-5706	48-00-8706	-	48-01-7706	100	
	8/12	12"	3/4"	0.050"	48-00-5094	-	48-01-6094	-	-	
<b>THE WRECKER™</b>	8	12"	1"	0.062"	48-00-5711	48-00-8711	-	48-01-7711	100	
	10/14	8"	5/8"	0.035"	48-00-5193	-	-	-	-	1/4" - 3/8"
	10/14	12"	5/8"	0.035"	48-00-5194	-	-	-	-	1/4" - 3/8"