

M18™ Metal Cutting Saw Kit

2682-22 (2682-20 Tool-Only)

Specifications:

RPM	3,600
Cut Capacity	1/8" – 2"
Blade Size	5-3/8"
Shoe	Stainless Steel
Weight	5.8 lbs



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, (1) 30T METAL TECH™ Carbide-Tipped Blade, Blade Wrench, Multi-Voltage Charger, Contractor Bag



M18™ Band Saw Kit

2629-22 (2629-20 Tool-Only)

Specifications:

SFPM	480
Cut Capacity	3-1/4" x 3-1/4"
Weight	10.2 lbs
Shoe	Tool Free
LED Light	Yes



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Blade, Multi-Voltage Charger, Carrying Case

M18™ Multi-Tool Kit

2626-22, 2626-22CT (2626-20 Tool-Only)

Specifications:

Speed Settings	12
OPM	11,000 – 18,000
Universal Adapter	Yes
Tool Free Accessory Change	Yes
Length	14"
Weight	4.2 lbs



Includes: 2626-22 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, (1) Wood Cutting Blade, (1) Sanding Pad, (5) Assorted Sanding Sheets, Multi-Voltage Charger, Contractor Bag; 2626-22CT Includes (2) M18™ REDLITHIUM™ Compact Battery Packs



M18 FUEL 4-1/2" / 5" Grinder Slide Switch, Lock-On Kit

2781-22, 2781-21 (2781-20 Tool-Only)

Specifications:

RPM	8,500
Power to Grind	Yes
Overload Protection	Yes
Electronic Clutch	Yes
Tool Free Accessory Change & Guard	Yes



Includes: 2781-22 (2) M18™ REDLITHIUM™ XC4.0 Battery Packs, Multi-Voltage Charger, Carrying Case; 2781-21 Includes (1) M18™ REDLITHIUM™ XC4.0 Battery Pack

M18 FUEL 4-1/2" / 5" Grinder Paddle Switch, No-Lock Kit

2780-22 (2780-20 Tool-Only)

Specifications:

RPM	8,500
Power to Grind	Yes
Overload Protection	Yes
Electronic Clutch	Yes
Tool Free Accessory Change & Guard	Yes



Includes: (2) M18™ REDLITHIUM™ XC4.0 Battery Packs, Multi-Voltage Charger, Carrying Case



M18™ 4-1/2" Cut-Off / Grinder Kit

2680-22 (2680-20 Tool-Only)

Specifications:

RPM	9,000
Switch	Paddle
Guard Adjustment	Tool Free
Overload Protection	Yes
Weight	5.9 lbs



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, (1) Type 1 Guard, (1) Type 27 Guard, (1) Spanner Wrench, (1) Side Handle, Multi-Voltage Charger, Contractor Bag

M18™ FORCE LOGIC™ Long Throw Press Tool Kit

2673-22L (2673-20L No Jaw Kit)

Specifications:

Capacity	1/2" – 4" CU, 1/2" – 2" SS
Weight	10.1 lbs
Length	20-1/8"
Calibration Interval	40,000 Cycles (LED Indicator)
Approximate Cycle Time	5 Seconds, 10 Seconds at Full Stroke
Press Force	7,200 lbs



Includes: 2673-22L (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, (3) Jaws 1/2" – 1", Multi-Voltage Charger, Carrying Case; 2673-20L Includes No Jaws

M18™ FORCE LOGIC™ Jaws and Rings - Stainless Steel

Specifications:

49-16-2650S	1/2" SS Jaw
49-16-2651S	3/4" SS Jaw
49-16-2652S	1" SS Jaw
49-16-2654S	1-1/2" SS Ring
49-16-2655S	2" SS Ring
49-16-2659S	SS Ring Jaw 2
49-16-2691	FORCE LOGIC SS Press Ring 1-1/2" – 2" Kit



Jaws and Rings designed for use with GRINNELL® G-Press Stainless Steel Fittings
Jaws compatible with both 2673-20 and 2673-20L M18™ Press Tools
Rings compatible with 2673-20L only

M18™ FORCE LOGIC™ Press Tool Kit

2673-22 (2673-20 No Jaw Kit)

Specifications:

Capacity	1/2" – 4" CU, 1/2" – 1" SS
Weight	8.0 lbs
Length	16-3/4"
Calibration Interval	40,000 Cycles (LED Indicator)
Approximate Cycle Time	5 Seconds
Press Force	7,200 lbs



Includes: 2673-22 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, (6) Jaws 1/2" – 2", Multi-Voltage Charger, Carrying Case; 2673-20 Includes No Jaws

M18™ FORCE LOGIC™ Jaws and Rings - Standard

Specifications:

49-16-2650	1/2" Jaw
49-16-2651	3/4" Jaw
49-16-2652	1" Jaw
49-16-2653	1-1/4" Jaw
49-16-2654	1-1/2" Jaw
49-16-2655	2" Jaw
49-16-2656	2-1/2" Ring
49-16-2657	3" Ring
49-16-2658	4" Ring
49-16-2659	Ring Jaw
49-16-2690	FORCE LOGIC™ Press Ring 2-1/2" – 4" Kit



Jaws designed for use with all major fitting manufacturers; Rings designed for use with VIEGA®, APOLLO®, and GRINNELL® large diameter copper systems

Jaws and Rings compatible with both 2673-20 and 2673-20L M18™ Press Tools

APOLLO® is a registered trademark of Conbraco Industries, Inc.
GRINNELL® is a registered trademark of Grinnell LLC
VIEGA® is a registered trademark of Viega GmbH & Co.



M18™ FORCE LOGIC™ High-Capacity Knockout Tool

2676-23, 2676-22 (2676-20 No Punches & Dies)

Specifications:

Mild Steel Capacity	1/2" – 4"
Stainless Steel Capacity	1/2" – 4"
Output Force	10 Ton
Quick-Connect Draw Stud	Yes
Tool Weight	7.2 lbs
Height	5-1/2"



Includes: 2676-23 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Exact™ Knockout Punches and Dies 1/2" – 4", (2) Draw Studs, Quick Connect Assembly, Carrying Case; 2673-22 Includes 1/2" – 2" Exact™ Knockout Punches and Dies; 2673-20 Includes no Punches or Dies

M18™ Exact™ Knockout Punches & Dies

Specifications:

Sets	
49-16-2694	EXACT™ KO Punch Set 1/2" – 2" w/ Wrench
49-16-2692	EXACT™ KO Punch Set 1/2" – 1-1/4"
49-16-2693	EXACT™ KO Punch Set 1/2" – 2"
49-16-2695	EXACT™ KO Punch Set 2-1/2", 3", 3-1/2", 4"

Open Stock

49-16-2660	1/2" Die
49-16-2661	1/2" Punch
49-16-2662	3/4" Die
49-16-2663	3/4" Punch
49-16-2664	1" Die
49-16-2665	1" Punch
49-16-2666	1-1/4" Die
49-16-2667	1-1/4" Punch
49-16-2668	1-1/2" Die
49-16-2669	1-1/2" Punch
49-16-2670	2" Die
49-16-2671	2" Punch
49-16-2672	2-1/2" Die
49-16-2673	2-1/2" Punch
49-16-2674	3" Die
49-16-2675	3" Punch
49-16-2676	3-1/2" Die
49-16-2677	3-1/2" Punch
49-16-2678	4" Die
49-16-2679	4" Punch
49-16-2621	3/8" Ball Bearing Draw Stud
49-16-2622	3/4" Ball Bearing Draw Stud
49-16-2680	7/16" Draw Stud
49-16-2681	3/4" Draw Stud
49-16-2682	1-1/8" Draw Stud

All EXACT™ Knockout Punches & Dies are designed for use in mild and stainless steel