

TE 2 & TE 2-S

Rotary Hammer Drills

- Multi-purpose hammer drill for fast drilling in concrete, block and masonry
- TE 2-S: Reduced hammering feature for drilling at brittle materials like tile and stone



Technical Data

Power input	600 W
Voltage	115 V
Hammering speed under load	0-4600 blows/min
Weight	TE 2: 5.1 lb TE 2-S: 5.3 lb

Drilling Range



TE-C (SDS)



Item No.	Description
228085	TE 2 Deluxe (115 V) Includes tool, 13 ft. supply cord, Hilti grease, cleaning cloth and operating instructions in an impact-resistant plastic tool box
383249	TE 2 Standard (115 V) Includes tool, 13 ft supply cord, side handle, depth gauge, dust shield and operating instructions in a cardboard box
3431651	TE 2-S Performance Package Includes tool plus one each of the following drill bits: TE-C3X 3/16" x 6", TE-C3X 1/4" x 4", TE-C3X 1/4" x 6", TE-C3X 5/16" x 6", TE-C3X 3/8" x 6" and TE-C3X 1/2" x 6"
228098	TE 2-S Deluxe (115 V) Includes tool, 13 ft. supply cord, Hilti grease, cleaning cloth and operating instructions in an impact-resistant plastic tool box

TE-C3X Carbide Tipped Fractional Bits



Single Pack Item No.	6-Pack Item No.	24-Pack Item No.	72-Pack Item No.	Description (dia x length)	Working length
206662	226964	226970	3427073	TE-C3X 3/16" x 4"	2"
206663	226965	226971	3425857	TE-C3X 3/16" x 6"	4"
206664	226966			TE-C3X 3/16" x 8"	5-1/2"
206667	206680	226972	3425858	TE-C3X 1/4" x 4"	2"
206668	206681	226973	3425859	TE-C3X 1/4" x 6"	4"
206669	226967			TE-C3X 1/4" x 8"	5-1/2"
206671	226968			TE-C3X 5/16" x 6"	4"
206674	206682	226974		TE-C3X 3/8" x 6"	4"
206675				TE-C3X 3/8" x 12"	9-1/2"
206678				TE-C3X 7/16" x 6"	4"
206711	206710	226975		TE-C3X 1/2" x 6"	4"
206712				TE-C3X 1/2" x 12"	9-1/2"
206714				TE-C3X 9/16" x 6"	4"
206717	226969			TE-C3X 5/8" x 8"	5-1/2"
375844				TE-CX 11/16" x 12"	9-1/2"
375846				TE-CX 3/4" x 8"	5-1/2"
375847				TE-CX 3/4" x 12"	9-1/2"
375849				TE-CX 13/16" x 18"	15-1/4"
375852				TE-CX 7/8" x 10"	7-1/2"
375854				TE-CX 1" x 10"	7-1/2"

TE-C Standard Carbide Bits



Single Pack Item No.	24-Pack Item No.	Description (dia x length)	Working length
385069	385498	TE-C 5/32" x 6"	4"
385070	385499	TE-C 3/16" x 4"	2"
385071	385500	TE-C 3/16" x 6"	4"
385072	385501	TE-C 1/4" x 4"	2"
385073	385502	TE-C 1/4" x 6"	4"
385074		TE-C 5/16" x 6"	4"
385076	385503	TE-C 3/8" x 6"	4"
385078		TE-C 7/16" x 6"	4"
385079		TE-C 7/16" x 12"	9-1/2"
385080	385504	TE-C 1/2" x 6"	4"
385081		TE-C 1/2" x 12"	9-1/2"
385083		TE-C 9/16" x 6"	4"
385085		TE-C 5/8" x 8"	5-1/2"
284333		TC-C 3/4" x 8"	5-1/2"
283910		TC-C 7/8" x 10"	7-1/2"
283911		TC-C 1" x 10"	7-1/2"

TE-C3X Trade Sets

Item No.	Description
226946	TE-C3X Performance Pack Includes 1 each TE-C3X: 3/16" x 6", 1/4" x 6", 5/16" x 6", 3/8" x 6", 1/2" x 6", 5/8" x 6"
226960	TE-C3X Universal Pack Includes 2 each TE-C3X: 1/4" x 6", 3/8" x 6", 1/2" x 6"
226953	TE-C3X Small Diameter Pack Includes 1 each TE-C3X: 3/16" x 6", 1/4" x 4", 1/4" x 6", 5/16" x 6", 3/8" x 6", 1/2" x 6"

Extension Cords

Outdoor Heavy Duty Extension Cords

Heavy Duty: 3 conductor, UL listed, lighted ends, SJTW

Item No.	Description
375965	12/3 x 50'
375966	12/3 x 100'
375967	14/3 x 50'
375968	14/3 x 100'

Accessories

Item No.	Description
375972	Super Premium Ground Fault Interrupter (GFI) 12/3 x 3' GFI x Three-way (15 A) lighted end



Hilti. Outperform. Outlast.